

Data sheet for SINAMICS Power module PM230

Article No. : 6SL3223-0DE31-8BA0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data

Input

Number of phases	3 AC
Line voltage	380 ... 480 V \pm 10 %
Line frequency	47 ... 63 Hz
Rated current (LO)	39.00 A
Rated current (HO)	33.00 A

Output

Number of phases	3 AC	
Rated voltage	400V IEC	480V NEC
Rated power (LO)	18.50 kW	25.00 hp
Rated power (HO)	15.00 kW	20.00 hp
Rated current (LO)	38.00 A	
Rated current (HO)	32.00 A	
Max. output current	64.00 A	
Pulse frequency	4 kHz	
Output frequency for vector control	0 ... 200 Hz	
Output frequency for V/f control	0 ... 550 Hz	

Overload capability

Low Overload (LO)

1.1 x rated output current (i.e. 110 % overload) for 57 s with a cycle time of 300 s
1.5 x rated output current (i.e. 150 % overload) for 3 s with a cycle time of 300 s

High Overload (HO)

1.5 x output current rating (i.e., 150 % overload) for 57 s with a cycle time of 300 s
2 x output current rating (i.e., 200 % overload) for 3 s with a cycle time of 300 s

General tech. specifications

Power factor λ	0.90
Offset factor $\cos \varphi$	0.95
Efficiency η	0.97
Sound pressure level (1m)	56 dB
Power loss	0.52 kW
Filter class (integrated)	Class B

Ambient conditions

Cooling	Internal air cooling
Cooling air requirement	0.039 m ³ /s (1.377 ft ³ /s)
Installation altitude	1,000 m (3,280.84 ft)

Ambient temperature

Operation LO	0 ... 40 °C (32 ... 104 °F)
Operation HO	0 ... 50 °C (32 ... 122 °F)
Transport	-25 ... 55 °C (-13 ... 131 °F)
Storage	-25 ... 55 °C (-13 ... 131 °F)

Relative humidity

Max. operation	95 % RH, condensation not permitted
----------------	-------------------------------------

Mechanical data

Degree of protection	IP55 / UL type 12
Size	FSD
Net weight	31.00 kg (68.34 lb)
Dimensions	
Width	320 mm (12.60 in)
Height	640 mm (25.20 in)
Depth	329 mm (12.95 in)

Connections

Line side

Version	M6 bolt
Conductor cross-section	16.00 ... 35.00 mm ² (AWG 6 ... AWG 2)

Motor end

Version	M6 bolt
Conductor cross-section	16.00 ... 35.00 mm ² (AWG 6 ... AWG 2)

Max. motor cable length


Shielded	25 m (82.02 ft)
Unshielded	100 m (328.08 ft)

Data sheet for SINAMICS Power module PM230

Article No. : 6SL3223-0DE31-8BA0

Converter losses to IEC61800-9-2*

Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	41.30 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

Standards

Compliance with standards	CE, C-Tick (RCM)
CE marking	Low-voltage directive 2006/95/EC