



Figure similar

MLFB-Ordering data

6SL3210-1RH31-2AL0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data	General tech. specifications
------------	------------------------------

Input

Number of phases	3 AC
Line voltage	500 ... 690 V $\pm 10\%$
Line frequency	47 ... 63 Hz
Rated current (LO)	111.00 A
Rated current (HO)	106.00 A

Output

Number of phases	3 AC
Rated voltage	690 V
Rated current (LO)	115.00 A
Rated current (HO)	100.00 A
Max. output current	156.00 A
Rated power IEC 690V (LO)	110.00 kW
Rated power NEC 600V (LO)	100.00 hp
Rated power IEC 690V (HO)	90.00 kW
Rated power NEC 600V (HO)	100.00 hp
Pulse frequency	2 kHz
Output frequency for vector control	0 ... 200 Hz
Output frequency for V/f control	0 ... 550 Hz

Overload capability

Low Overload (LO)

1.1 x rated output current (i.e. 110 % overload) for 57 s with a cycle time of 300 s 1.35 x rated output current (i.e. 135 % overload) for 3 s with a cycle time of 300 s

High Overload (HO)

1.5 x output current rating (i.e., 150 % overload) for 60 s with a cycle time of 300 s

Power factor λ	0.90
Offset factor $\cos \phi$	0.99
Efficiency η	0.99
Sound pressure level (1m)	68 dB
Power loss	1.97 kW
Filter class (integrated)	Class A

Ambient conditions

Cooling	Internal air cooling
Cooling air requirement	0.153 m ³ /s (5.403 ft ³ /s)
Installation altitude	1000 m (3280.84 ft)

Ambient temperature

Operation LO	-20 ... 40 °C (-4 ... 104 °F)
Operation HO	-20 ... 50 °C (-4 ... 122 °F)
Transport	-40 ... 70 °C (-40 ... 158 °F)
Storage	-40 ... 70 °C (-40 ... 158 °F)

Relative humidity

Max. operation	95 % RH, condensation not permitted
----------------	-------------------------------------



Figure similar

MLFB-Ordering data


6SL3210-1RH31-2AL0

Mechanical data

Degree of protection	IP20 / UL open type
Size	FSF
Net weight	64.00 kg (141.10 lb)
Width	305 mm (12.01 in)
Height	708 mm (27.87 in)
Depth	357 mm (14.06 in)

Converter losses to EN 50598-2*

Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	-0.35 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard EN 50598) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

Connections

Line side

Version	M10 bolt
Conductor cross-section	35.00 ... 120.00 mm ² (AWG 2 ... AWG -3)

Motor end

Version	M10 bolt
Conductor cross-section	35.00 ... 120.00 mm ² (AWG 2 ... AWG -3)

Max. motor cable length

Shielded	300 m (984.25 ft)
Unshielded	450 m (1476.38 ft)

Standards

Compliance with standards UL, cUL, CE, C-Tick (RCM), SEMI F47

CE marking Low-voltage directive 2006/95/EC