

## Data sheet for SINAMICS V20

Article No. : 6SL3210-5BB11-2AV0



Figure similar

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

### Rated data

#### Input

Number of phases	1 AC
Line voltage	200 ... 240 V -10 % +10 %
Line frequency	47 ... 63 Hz

#### Output

Number of phases	3 AC	
<b>Rated voltage</b>	<b>230V IEC</b>	<b>240V NEC <sup>1)</sup></b>
Rated power (LO)	0.12 kW	0.16 hp
Rated power (HO)	0.12 kW	0.16 hp
Rated current (LO)	0.90 A	0.90 A
Rated current (HO)	0.90 A	0.90 A
Rated current (IN)	0.90 A	
Pulse frequency	8.00 kHz	
Output frequency	0 ... 550 Hz	

#### Overload capability

Low Overload (LO)
110 % rated output current for 60 s, cycle time 300 s
High Overload (HO)
150 % rated output current for 60 s, cycle time 300 s

### General tech. specifications

Power factor $\lambda$	0.72
Offset factor $\cos \varphi$	0.95
Efficiency $\eta$	0.98
Filter class (integrated)	Class A

### Communication

Communication	USS, Modbus RTU
---------------	-----------------

### Inputs / outputs

#### Standard digital inputs

Number	4
--------	---

#### Digital outputs

Number as relay changeover contact	1
Number as transistor	1

#### Analog inputs

Number	2 (Can be used as additional digital input)
--------	---

#### Analog outputs

Number	1
--------	---

### Ambient conditions

Cooling	convection cooling
Installation altitude	1,000 m (3,280.84 ft)

#### Ambient temperature

Operation	-10 ... 60 °C (14 ... 140 °F)
Storage	-40 ... 70 °C (-40 ... 158 °F)

#### Relative humidity

Max. operation	95 %
----------------	------

### Connections

#### Max. motor cable length

Shielded	10 m (32.81 ft)
Unshielded	50 m (164.04 ft)

### Mechanical data

Mounting position	Wall mounting / side-by-side mounting
Degree of protection	IP20 / UL open type
Frame size	FSA
Net weight	1.10 kg (2.43 lb)

#### Dimensions

Width	90.0 mm (3.54 in)
Height	150.0 mm (5.91 in)
Depth	145.5 mm (5.73 in)

### Standards

Compliance with standards	CE, cULus, C-Tick (RCM), KC
CE marking	EN 61800-5-1 / EN 60204-1 and EN 61800-3

<sup>1)</sup>The output current and HP ratings are valid for the voltage range 220V-240V