

SIEMENS



Product overview for Comfort Panel Pro

TIA Selection Tool Web



SIMATIC HMI Comfort Panels PRO

SIMATIC HMI PRO - fully-enclosed IP65 protection without compromise

SIMATIC Comfort Panels PRO are a series of devices with high IP65 (NEMA4) degree of protection and flexible mounting options - directly on the machine using special adapters, on a pedestal or on a support arm system.

Thanks to their high performance, functionality and numerous integrated interfaces, they offer maximum convenience for high-end applications and are especially suitable for implementing high-performance visualization tasks in machine-level areas.

<http://www.siemens.com/simatic-hmi-pro>

Highlights

Modern design and universal scalability create flexible application options

- Slim enclosure with small depth, new scratch-resistant glass front and narrow frame.
- Devices can be dimensioned to suit machines and applications through a flexible selection of device type, performance class and display size.
- Individual selection and combination of basic units, expansion components and mounting options.
- High fully-enclosed IP65 degree of protection (against water and dust).
- Individual expandability through extension units.

Different operating options ensure high operating convenience

- Gesture, single and multiple finger operation (even with thin working gloves).
- Individual design by selecting your own design or style.

High flexibility in the place of use and easy connection

- Devices including extensions can be mounted to support arm and pedestal systems of different manufacturers using a flexible mechanism. Separate handle extension provides even more operating convenience.
- Simple connection and minimized wiring through communication with PROFINET and PROFI-safe.

High level of service friendliness leads to cost and time savings

- Rear panel can be easily removed even when the machine is mounted, e.g. for subsequent cabling or replacement of memory cards.

High reliability and operating safety creates long-term availability

- High operating safety through PROFI-safe, two-hand operation and palm recognition.


Fast commissioning provides cost savings

- Simple installation and configuration (Plug & Play) and easy changeover from a predecessor to a new device.
- Configuration in TIA Portal reduces costs during commissioning.


Protection of processes and plants against unauthorized access

- Plant protection through key switches and RFID access authorization as well as optional safety elements such as emergency stop.

Comfort Panel Pro

	Article number	
	SIMATIC HMI TP1200 Comfort Pro	6AV2124-0MC24-1AX0
	SIMATIC HMI TP1200 Comfort Pro	6AV2124-0MC24-0AX0
	SIMATIC HMI TP1200 Comfort Pro	6AV2124-0MC24-0BX0
	SIMATIC HMI TP1500 Comfort PRO	6AV2124-0QC24-0AX0
	SIMATIC HMI TP1500 Comfort PRO	6AV2124-0QC24-1AX0
	SIMATIC HMI TP1500 Comfort PRO	6AV2124-0QC24-0BX0
	SIMATIC HMI TP1900 Comfort PRO	6AV2124-0UC24-0AX0
	SIMATIC HMI TP1900 Comfort PRO	6AV2124-0UC24-1AX0
	SIMATIC HMI TP1900 Comfort PRO	6AV2124-0UC24-0BX0
	SIMATIC HMI TP2200 Comfort PRO	6AV2124-0XC24-0AX0
	SIMATIC HMI TP2200 Comfort PRO	6AV2124-0XC24-1AX0
	SIMATIC HMI TP2200 Comfort PRO	6AV2124-0XC24-0BX0


Extension Units

	Article number	
	Hardwired	
	Extension Unit 12" hardwired	6AV7674-1LA31-0AA0
	Extension Unit 15" hardwired	6AV7674-1LA41-0AA0
	Extension Unit 19" hardwired	6AV7674-1LA51-0AA0
	Extension Unit 22" hardwired	6AV7674-1LA61-0AA0
	PROFINET	
	Extension Unit 12" PROFINET	6AV7674-1LA32-0AA0
	Extension Unit 12" KP12 PN	6AV2185-8CE01-0AA0
	Extension Unit 12" KP24 PN	6AV2185-8CE08-0AA0
	Extension Unit 15" PROFINET	6AV7674-1LA42-0AA0
	Extension Unit 15" KP12 PN	6AV2185-8DE01-0AA0
	Extension Unit 15" KP36 PN	6AV2185-8DE08-0AA0
	Extension Unit 19" PROFINET	6AV7674-1LA52-0AA0
	Extension Unit 19" KP12 PN	6AV2185-8EE01-0AA0
	Extension Unit 19" KP36 PN	6AV2185-8EE08-0AA0
	Extension Unit 22" PROFINET	6AV7674-1LA62-0AA0
	Extension Unit 22" KP12 PN	6AV2185-8FE01-0AA0
	Extension Unit 22" KP48 PN	6AV2185-8FE08-0AA0
	Profisafe	
Extension Unit 12" PROFISAFE	6AV7674-1LA33-0AA0	
Extension Unit 12" KP12F PN	6AV2185-8CF01-0AA0	
Extension Unit 15" PROFISAFE	6AV7674-1LA43-0AA0	
Extension Unit 15" KP12F PN	6AV2185-8DF01-0AA0	
Extension Unit 19" PROFISAFE	6AV7674-1LA53-0AA0	
Extension Unit 19" KP12F PN	6AV2185-8EF01-0AA0	
Extension Unit 22" PROFISAFE	6AV7674-1LA63-0AA0	
Extension Unit 22" KP12F PN	6AV2185-8FF01-0AA0	


 : Safety-related component

* By clicking on the article number, you will be taken to the product in the TIA Selection Tool cloud.

Operator controls

	Article number	
	E-Stop Pushbutton for Ext. Unit	6AV7674-1MA00-0AA0
	Illuminated Pushbutton for Ext. Unit	6AV7674-1MB00-0AA0
	Indicator Light for Ext. Unit	6AV7674-1MC00-0AA0
	Selector Switch for Ext. Unit	6AV7674-1MD00-0AA0
	Key-operated Switch for Ext. Unit	6AV7674-1ME00-0AA0
	Reader RF1040R USB/RS232	6GT2831-6CA50
	Reader RF1060R USB	6GT2831-6AA50
	Reader RF1070R USB/RS232	6GT2831-6BA50
	RGB button	6AV2185-8AB01-2AA0
	Illum. pushbutton for ext.unit (1NO+1NC)	6AV7674-1MG00-0AA0
	USB interface for extension unit	6AV7674-1MF00-0AA0

Accessories

	Article number	
	Flange Mount for Pro Devices	6AV7674-1KF00-0AA0
	USB Interface for Pro Devices	6AV7674-1LX00-0AA0
	USB keyboard INT for 16:9 PRO devices	6AV7674-1NE00-0AA0
	Shelf for 16:9 PRO devices	6AV7674-1NE01-0AA0
	Label Inserts for Self Inscription	6AV7674-1LB30-0AA0
	12 Label Holder for Self Inscription	6AV7674-1LB20-0AA0

 : Safety-related component

* By clicking on the article number, you will be taken to the product in the TIA Selection Tool cloud.

Published by
Siemens AG

Digital Industries
Factory Automation
P.O. box 4848
90026 Nuremberg
Germany

For U.S. only:
Siemens Industry Inc.

100 Technology Drive
Alpharetta, GA 30005
United States

Copyright© 2022 Siemens

The TIA SELECTION TOOL and all its editions are made available to you at no charge. We therefore do not assume any warranty, in particular for the accuracy, correctness, completeness, availability or usability of this tool. Our liability for damages resulting from using the examples, help notes, programs, configuration and performance data, etc. described in this TIA SELECTION TOOL and all its editions regardless of the legal background is excluded unless required by law, e.g. in cases of willful misconduct, gross negligence, personal injury or death, failure to achieve guaranteed characteristics or fraudulent concealment of a defect or in case of breach of fundamental contractual obligations. Distribution or reproduction of this TIA SELECTION TOOL and all its editions or excerpts from it is prohibited unless expressly permitted by Siemens. The latest firmware and hardware versions are configured in the TIA Selection Tool.