

SIEMENS



Product overview for SIMATIC ET 200eco PN



SIMATIC ET 200eco PN

Maximum ruggedness for extremely challenging ambient conditions

SIMATIC ET 200eco PN is a compact block I/O with PROFINET connection with IP65/67 degree of protection for cabinet-free configuration directly at the machine – for example in machine manufacturing or in the automotive industry.

<https://www.siemens.com/et200ecopn>

Highlights

Flexible installation

- Easy to install in any position, vertical as well as horizontal installation.
- Can be mounted frontally or transversely directly on site in a machine or assembly line.
- Installation is possible on a level base, a mounting rail as well as on aluminum support beams using slot stones.

Fieldbus connection

- Harmonized range of modules for applications and integration into PROFINET applications.
- PROFINET is connected to the ET 200eco PN with an M12 connector and can be looped through to an additional PROFINET device.
- With ET 200eco PN, you can process digital, fail-safe digital, analog and IO-Link signals with PROFINET.

Power supply

Two power supplies are available. They are used by the I/O device and can also be looped through to an additional I/O device (line topology). 2x 12 A can be supplied or forwarded to I/O devices with an M12-L coded power plug and 2x 4 A can be supplied or forwarded to I/O devices with an M12-A coded power plug.

For I/O devices with M12-A coded power plug, the power supplies can be alternatively supplied and forwarded with up to 10 A via an additional terminal block.

I/O devices with M12-L coded power plug

- Greater current carrying capacity.
- Longer cable distances in the field without additional supply cables.

High robustness fulfils degree of protection IP65/67

- Very rugged die-cast zinc housing.
- Resistant to vibrations, dust, oil or humidity.
- Suitable for use in temperatures from -40 to +60 °C.

Integrated 2-port switch

Thanks to the integrated 2-port switch, the SIMATIC ET 200ecoPN configuration is flexible and can be extended via PROFINET and integrated into line topologies within a plant.

Isochronous mode

In PROFINET IRT networks, the I/O devices of the SIMATIC ET 200eco PN of the new generation can be operated in isochronous mode. This results in improved deterministics and thus better machine performance.

MSI – MSO

Thanks to Module-internal-Shared-Input (MSI) and Module-internal-Shared-Output (MSO), multiple controllers can simultaneously and independently read the current switching status of the inputs and outputs of a SIMATIC ET 200eco PN I/O device without additional programming.

Shared Device

The "Shared Device" function enables distribution of channels of an I/O device between two IO controllers. This distribution opens up flexible automation concepts.

IO-Link connection enables easy integration of sensors and actuators

The IO-Link master according to IO-Link specification V1.1 offers automatic restoration of the device parameters, master backup, configuration changes to the devices during operation and extensive diagnostic options. The IO-Link configuration can be performed via GSD file or S7-PCT.

Electronic modules

	Article number
	Digital inputs Compare technical specifications online ET200eco PN, 8DI, DC24V, 4xM12 6ES7141-6BF00-0AB0 ET200eco PN, 8DI, DC24V, 8xM12 6ES7141-6BG00-0AB0 ET 200eco PN, DI 8x24VDC, M12-L 6ES7141-6BG00-0BB0 ET200eco PN, 16DI, DC24V, 8xM12 6ES7141-6BH00-0AB0 ET 200eco PN, DI 16x24VDC, M12-L 6ES7141-6BH00-0BB0
	Digital outputs Compare technical specifications online ET200eco PN, 8DO, DC24V/1,3A, 4xM12 6ES7142-6BF00-0AB0 ET200eco PN, 8DO, DC24V/0,5A, 4xM12 6ES7142-6BF50-0AB0 ET 200eco PN, DQ 8x24VDC/0,5A, M12-L 6ES7142-6BG00-0BB0 ET200eco PN, 8DO, DC24V/1,3A, 8xM12 6ES7142-6BG00-0AB0 ET200eco PN, 16DO DC24V/1,3A, 8xM12 6ES7142-6BH00-0AB0 ET200eco PN, 8 DO, DC24V/2A, 8xM12 6ES7142-6BR00-0AB0 ET 200eco PN, DQ 8x24VDC/2A, M12-L 6ES7142-6BR00-0BB0
	Digital inputs/outputs Compare technical specifications online ET200eco PN, 8 DIO, DC24V/1,3A, 8xM12 6ES7147-6BG00-0AB0 ET 200eco PN, DIQ 16x24VDC/2A, M12-L 6ES7143-6BH00-0BB0 ET 200eco PN, F-DI 8x24V /F-DQ 3x24V 2A 6ES7146-6FF00-0AB0
	Analog inputs Compare technical specifications online ET200eco PN, 8AI; 4 U/I; 4 RTD/TC 8xM12 6ES7144-6KD00-0AB0 ET200eco PN, 8AI RTD/TC 8xM12 6ES7144-6KD50-0AB0 ET 200eco PN, AI 8xRTD/TC, M12-L 6ES7144-6JF00-0BB0
	Analog outputs Compare technical specifications online ET200eco PN, 4AO U/I 4xM12 6ES7145-6HD00-0AB0
	Analog inputs/outputs Compare technical specifications online ET 200eco PN, AI 6xU/I + AIQ 2xU/I, M12-L 6ES7146-6HF00-0BB0
	IO-Link master Compare technical specifications online ET 200eco PN, 4xIO-Link + 8DI/4DO, 8xM12 6ES7148-6JA00-0AB0 ET 200eco PN, 4xIO-Link 4xM12 6ES7148-6JD00-0AB0 ET 200eco PN, CM 8x IO-Link, M12-L 6ES7148-6JG00-0BB0 ET 200eco PN, CM 4x IO-Link, M12-L 6ES7148-6JE00-0BB0 ET 200eco PN, CM 8x IO-Link, M12-L 6ES7148-6JJ00-0BB0

Accessories

	Article number
	Terminal block Terminal Block for ET200eco PN 6ES7194-6CA00-0AA0 Replacement Fuse Terminal Block 6ES7194-6HB00-0AA0
	Energy distribution and measurement Compare technical specifications online ET200eco PN, Power Distributor DC24V 6ES7148-6CB00-0AA0
	Connectors and cables for power supply M12-A Power Connecting Cable 0,3m 6XV1801-5DE30 Power Connecting Cable 0,5m 6XV1801-5DE50 Power Connecting Cable 1,0m 6XV1801-5DH10 Power Connecting Cable 1,5m 6XV1801-5DH15 Power Connecting Cable 2,0m 6XV1801-5DH20 Power Connecting Cable 3,0m 6XV1801-5DH30 Power Connecting Cable 5,0m 6XV1801-5DH50 Power Connecting Cable 10m 6XV1801-5DN10 Power Connecting Cable 15m 6XV1801-5DN15 IE Power M12 Plug PRO 6GK1907-0DB10-6AA3 M12 PROFIBUS SOCKET ANGLED 3RK1902-4DA00-5AA0

 : Safety-related component

* By clicking on the article number, you will be taken to the product in the TIA Selection Tool cloud.

Accessories

	Article number
IE Power M12 Cable Connector PRO	6GK1907-0DC10-6AA3
M12 PROFIBUS SOCKET ANGLED	3RK1902-4CA00-4AA0
ROBUST POWER CONNECTING CABLE 1.0 M	6XV1801-5AH10
ROBUST POWER CONNECTING CABLE 2.0 M	6XV1801-5AH20
ROBUST POWER CONNECTING CABLE 3.0 M	6XV1801-5AH30
ROBUST POWER CONNECTING CABLE IP69 5M	6XV1801-5AH50
Power Connecting Cable 0.3 m	6XV1801-5GE30
Power Connecting Cable 0.5 m	6XV1801-5GE50
Power Connecting Cable 1 m	6XV1801-5GH10
Power Connecting Cable 1.5 m	6XV1801-5GH15
Power Connecting Cable 2 m	6XV1801-5GH20
Power Connecting Cable 3 m	6XV1801-5GH30
Power Connecting Cable 5 m	6XV1801-5GH50
Power Connecting Cable 10 m	6XV1801-5GN10
Power Connecting Cable 15 m	6XV1801-5GN15
Connectors and cables for power supply M12-L	
Power M12 Plug Pro (L-coded)	6GK1906-0EA00
Power M12 Cable Connector Pro (L-coded)	6GK1906-0EB00
Energy Cable 4-wired by meter	6XV1801-2B
Power Connecting Cable 0,5 m, L-Coded	6XV1801-6DE50
Power Connecting Cable 1,0 m, L-Coded	6XV1801-6DH10
Power Connecting Cable 1,5 m, L-Coded	6XV1801-6DH15
Power Connecting Cable 2,0 m, L-Coded	6XV1801-6DH20
Power Connecting Cable 3,0 m, L-Coded	6XV1801-6DH30
Power Connecting Cable 5,0 m, L-Coded	6XV1801-6DH50
Power Connecting Cable 10,0 m, L-Coded	6XV1801-6DN10
Power Connecting Cable 15,0 m, L-Coded	6XV1801-6DN15
Power Connecting Cable, 0,5 M, L-coded	6XV1801-6GE50
Power Connecting Cable, 1,0 M, L-coded	6XV1801-6GH10
Power Connecting Cable, 1,5 M, L-coded	6XV1801-6GH15
Power Connecting Cable, 2,0 M, L-coded	6XV1801-6GH20
Power Connecting Cable, 3,0 M, L-coded	6XV1801-6GH30
Power Connecting Cable, 5,0 M, L-coded	6XV1801-6GH50
Power Connecting Cable, 10,0 M, L-coded	6XV1801-6GN10
Power Connecting Cable, 15,0 M, L-coded	6XV1801-6GN15
Connectors and cables for power supply 7/8"	
7/8 Connector	6GK1905-0FB00
7/8 SOCKET FOR 24 VOLT ANGLED	3RK1902-3DA00
Energy Cable 5 core, by meter	6XV1830-8AH10
7/8 Connecting cable 1.5 m	6XV1822-5BH15
7/8" CONNECTING CABLE 2.0 M	6XV1822-5BH20
7/8" CONNECTING CABLE 3 M	6XV1822-5BH30
7/8 Connecting cable 5 m	6XV1822-5BH50
7/8 Connecting cable 10 m	6XV1822-5BN10
7/8 Connecting cable 15 m	6XV1822-5BN15
ENERGY CABLE 24V 3 M BOTH SIDES	3RK1902-3NB30
ENERGY CABLE 24V - 5 M - BOTH SIDES	3RK1902-3NB50
ENERGY CABLE 24V - 10 M	3RK1902-3NC10
ENERGY CABLE 24V 3 M ONE SIDED	3RK1902-3GB30
BUS CABLE 24V 5 M ONE SIDED	3RK1902-3GB50
ENERGYCABLE 24VOLT 10 M	3RK1902-3GC10
PROFINET connectors and cables	
IE FC M12 Plug PRO 2x2	6GK1901-0DB20-6AA0
IE FC M12 Plug PRO 2x2	6GK1901-0DB20-6AA8

 : Safety-related component

* By clicking on the article number, you will be taken to the product in the TIA Selection Tool cloud.

Accessories

	Article number
IE M12 Plug PRO (1 piece)	6GK1901-0DB10-6AA0
IE M12 Plug PRO (8 piece)	6GK1901-0DB10-6AA8
M12 PROFINET PLUG ANGLED	3RK1902-2DA00
IE FC TP Standard Cable GP2x2 by meter	6XV1840-2AH10
IE FC TP Trailing Cable 2x2 by meter	6XV1840-3AH10
IE FC TP Trailing Cable 2x2 by meter	6XV1870-2D
IE FC TP Marine Cable sold by meter	6XV1840-4AH10
IE TP Torsion Cable 2x by meter	6XV1870-2F
IE Connecting Cable M12-180/M12-180 0,3m	6XV1870-8AE30
IE Connecting Cable M12-180/M12-180 0,5m	6XV1870-8AE50
IE Connecting Cable M12-180/M12-180 1 m	6XV1870-8AH10
IE Connecting Cable M12-180/M12-180 1,5m	6XV1870-8AH15
IE Connecting Cable M12-180/M12-180 2 m	6XV1870-8AH20
IE Connecting Cable M12-180/M12-180 3 m	6XV1870-8AH30
IE Connecting Cable M12-180/M12-180 5 m	6XV1870-8AH50
IE Connecting Cable M12-180/M12-180 10 m	6XV1870-8AN10
IE Connecting Cable M12-180/M12-180 15 m	6XV1870-8AN15
BUS CABLE PROFINET 3 M BOTH SIDES	3RK1902-2NB30
BUS CABLE PROFINET 5 M BOTH SIDES	3RK1902-2NB50
BUS CABLE PROFINET 3 M	3RK1902-2HB30
BUS CABLE PROFINET 10 M BOTH SIDES	3RK1902-2NC10
BUS CABLE PROFINET 5 M	3RK1902-2HB50
BUS CABLE PROFINET 10 M	3RK1902-2HC10
IE Connecting Cable M12-180/RJ45, 2 m	6XV1871-5TH20
IE Connecting Cable M12-180/RJ45, 3 m	6XV1871-5TH30
IE Connecting Cable M12-180/RJ45, 5 m	6XV1871-5TH50
IE Connecting Cable M12-180/RJ45, 10 m	6XV1871-5TN10
IE Connecting Cable M12-180/RJ45, 15 m	6XV1871-5TN15
IE Robust Connecting Cable M12 IP69, 1 m	6XV1881-5AH10
IE Robust Connecting Cable M12 IP69, 2 m	6XV1881-5AH20
IE Robust Connecting Cable M12 IP69, 3 m	6XV1881-5AH30
IE Robust Connecting Cable M12 IP69, 5 m	6XV1881-5AH50
IE Connecting Cable M12-90/M12-90, 0,3m	6XV1870-8GE30
IE Connecting Cable M12-90/M12-90, 0,5m	6XV1870-8GE50
IE Connecting Cable M12-90/M12-90, 1 m	6XV1870-8GH10
IE Connecting Cable M12-90/M12-90, 1,5m	6XV1870-8GH15
IE Connecting Cable M12-90/M12-90, 2 m	6XV1870-8GH20
IE Connecting Cable M12-90/M12-90, 3 m	6XV1870-8GH30
IE Connecting Cable M12-90/M12-90, 5 m	6XV1870-8GH50
IE Connecting Cable M12-90/M12-90, 10 m	6XV1870-8GN10
IE Connecting Cable M12-90/M12-90, 15 m	6XV1870-8GN15
Accessories M8, M12	
AS-I CAP PLUGS	3RX9802-0AA00
AS-INTERFACE, BLANK PLUG	3RK1901-1KA00
M12 CONNECTOR STRAIGHT	3RK1902-4BA00-5AA0
M12 PROFIBUS SOCKET ANGLED	3RK1902-4DA00-5AA0
M12 - M12 CABLE 1.5M 3 POLE	3RK1902-4PB15-3AA0
M12 PROFIBUS SOCKET ANGLED	3RK1902-4HB15-5AA0
M12 PROFIBUS SOCKET ANGLED	3RK1902-4HB50-5AA0
M12 PROFIBUS SOCKET ANGLED	3RK1902-4HC01-5AA0
ET200, Y Cable	6ES7194-6KA00-0XA0
ET200, Y cable	6ES7194-6KB00-0XA0
ET200, Y cable	6ES7194-6KC00-0XA0
ET200, Y Connector	6ES7194-1KA01-0XA0

 : Safety-related component

* By clicking on the article number, you will be taken to the product in the TIA Selection Tool cloud.

Accessories

	Article number
E coding plug, IP 65/67	6ES7194-6KB01-0AA0
ET200, Compensation Connector	6ES7194-4AB00-0AA0
Control Cable 5 core cable sold by meter	6XV1801-2C
Accessories M12	
Conn. Cable IO-Link, 2 X M12-4pin, 5m	6GT2891-4MH50
Conn. Cable IO-Link, 2 X M12-4pin, 10m	6GT2891-4MN10
Control Connecting Cable M12/M12, 0,5m	6XV1801-2CE50
Control Connecting Cable M12/M12, 1,0m	6XV1801-2CH10
Control Connecting Cable M12/M12, 1,0m	6XV1801-2CH15
Control Connecting Cable M12/M12, 2,0m	6XV1801-2CH20
Control Connecting Cable M12/M12, 3,0m	6XV1801-2CH30
Control Connecting Cable M12/M12, 5,0m	6XV1801-2CH50
Control Connecting Cable M12/M12, 10,0m	6XV1801-2CN10
Control Connecting Cable M12/M12, 15,0m	6XV1801-2CN15
ET200, Y Connector	6ES7194-1KA01-0XA0
Control M12 Cable Connector PRO	6GK1908-0DC10-6AA0
DIN rails	
Mounting BAR for ET200eco PN	6ES7194-6GA00-0AA0
Self-tapping Screw for ET200eco PN	6ES7194-6MA00-0AA0
Identification labels	
IDENTIFICATION LABELS 10X7 MM, RAL6034	3RT1900-1SB10
Identification Labels 10x5 mm, RAL9016	6ES7194-2BA00-0AA0
Plug cover	
Connector cover for ET200ecoPN M12-L	6ES7194-6JA00-0BB0

[Compare technical specifications online](#)
 : Safety-related component

* By clicking on the article number, you will be taken to the product in the TIA Selection Tool cloud.

Published by
Siemens AG

Digital Industries
Factory Automation
P.O. box 4848
90026 Nuremberg
Germany

For U.S. only:
Siemens Industry Inc.

100 Technology Drive
Alpharetta, GA 30005
United States

Copyright © Siemens 2012 - 2024

The TIA SELECTION TOOL and all its editions are made available to you at no charge. We therefore do not assume any warranty, in particular for the accuracy, correctness, completeness, availability or usability of this tool. Our liability for damages resulting from using the examples, help notes, programs, configuration and performance data, etc. described in this TIA SELECTION TOOL and all its editions regardless of the legal background is excluded unless required by law, e.g. in cases of willful misconduct, gross negligence, personal injury or death, failure to achieve guaranteed characteristics or fraudulent concealment of a defect or in case of breach of fundamental contractual obligations. Distribution or reproduction of this TIA SELECTION TOOL and all its editions or excerpts from it is prohibited unless expressly permitted by Siemens. The latest firmware and hardware versions are configured in the TIA Selection Tool.