

## Data sheet for SINAMICS Power module PM250

Article No. : 6SL3225-0BE35-5AA0



Figure similar

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

### Rated data

#### Input

Number of phases	3 AC
Line voltage	380 ... 480 V $\pm$ 10 %
Line frequency	47 ... 63 Hz
Rated current (LO)	135.00 A
Rated current (HO)	102.00 A

#### Output

Number of phases	3 AC	
<b>Rated voltage</b>	<b>400V IEC</b>	<b>480V NEC</b>
Rated power (LO)	75.00 kW	100.00 hp
Rated power (HO)	55.00 kW	75.00 hp
Rated current (LO)	145.00 A	
Rated current (HO)	110.00 A	
Max. output current	220.00 A	
Pulse frequency	4 kHz	
Output frequency for vector control	0 ... 200 Hz	
Output frequency for V/f control	0 ... 550 Hz	

#### Overload capability

##### Low Overload (LO)

1.1 x rated output current (i.e. 110 % overload) for 57 s with a cycle time of 300 s  
1.5 x rated output current (i.e. 150 % overload) for 3 s with a cycle time of 300 s

##### High Overload (HO)

1.5 x output current rating (i.e., 150 % overload) for 57 s with a cycle time of 300 s  
2 x output current rating (i.e., 200 % overload) for 3 s with a cycle time of 300 s

### General tech. specifications

Power factor $\lambda$	0.90
Offset factor $\cos \varphi$	0.95
Efficiency $\eta$	0.97
Sound pressure level (1m)	60 dB
Power loss	1.93 kW
Filter class (integrated)	Class A

### Ambient conditions

Cooling	Internal air cooling
Cooling air requirement	0.094 m <sup>3</sup> /s (3.320 ft <sup>3</sup> /s)
Installation altitude	1,000 m (3,280.84 ft)
<b>Ambient temperature</b>	
Operation LO	0 ... 40 °C (32 ... 104 °F)
Operation HO	0 ... 50 °C (32 ... 122 °F)
Transport	-25 ... 55 °C (-13 ... 131 °F)
Storage	-25 ... 55 °C (-13 ... 131 °F)

#### Relative humidity

Max. operation	95 % RH, condensation not permitted
----------------	-------------------------------------

### Mechanical data

Degree of protection	IP20 / UL open type
Size	FSF
Net weight	51.00 kg (112.44 lb)
<b>Dimensions</b>	
Width	350 mm (13.78 in)
Height	934 mm (36.77 in)
Depth	316 mm (12.44 in)

### Connections

#### Line side

Version	M8 bolt
Conductor cross-section	25.00 ... 120.00 mm <sup>2</sup> (AWG 4 ... AWG -3)

#### Motor end

Version	M8 bolt
Conductor cross-section	25.00 ... 120.00 mm <sup>2</sup> (AWG 4 ... AWG -3)

#### Max. motor cable length


Shielded	50 m (164.04 ft)
Unshielded	100 m (328.08 ft)

## Data sheet for SINAMICS Power module PM250

Article No. : 6SL3225-0BE35-5AA0

### Converter losses to IEC61800-9-2\*

Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	52.67 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*converted values

### Standards

Compliance with standards	CE, C-Tick (RCM)
CE marking	Low-voltage directive 2006/95/EC