

MLFB-Ordering data 6FX2001-3CB00



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Electrical data		Mechanical data	
Operating voltage Up	DC 5 V ± 10 %	Shaft diameter	6 mm
Max. power consumption without	150 mA	Shaft length	10 mm
Signal level	Sinusoidal 1 Vpp	Angular acceleration, max.	100000 rad/s²
Resolution	1000 S/R	Moment of inertia of rotor	0.00000145 kgm²
Accuracy	65 rad	Vibration (55...2000 Hz), max.	300
Phase relation signal A to B	90° ± 10 %	Friction torque (at 20°C), max.	0.01 Nm
Limit frequency type at		Starting torque (at 20°C), max.	0.01 Nm
-3 dB	>= 100 kHz	Net weight	0.3 kg
-6 dB	>= 200 kHz	Max. admissible speed	
Cable length		Electrical	18000 rpm
To the downstream electronics,	150 m	Mechanical	12000 rpm
Ambient temp in operation		Load capacity	
Fixed installation of flange outlet or cable		n <= 6000 rpm	
- At Up = 5V ± 10%	-40 ... 100 °C	- Axial	40 N
Flexible cable		- Radial at shaft end	60 N
- At Up = 5V ± 10%	-10 ... 100 °C	n > 6000 rpm	
Standards		- Axial	10 N
Compliance with standards	CE, cULus	- Radial at shaft end	20 N
EMC class filter	Tested according to the EMC guidelines 89/336/EEC and the rules of the EMC guidelines (generic standards)	Shock, max.	
		2 ms	2000 m/s²
		6 ms	1000 m/s²
		Degree of protection	
		Without shaft input	IP67
		With shaft input	IP64