

MLFB-Ordering data                      6FX2001-4DA10



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Electrical data		Mechanical data	
Operating voltage Up	DC 10 ... 30 V	Shaft diameter	6 mm
Max. power consumption without	150 mA	Shaft length	10 mm
Signal level	UH >= 21 V at IH = 20 mA at 24 V; UL <= 2,8 V at IL = 20 mA at 24 V	Angular acceleration, max.	100000 rad/s²
		Moment of inertia of rotor	0.00000145 kgm²
Resolution	100 S/R	Vibration (55...2000 Hz), max.	300 m/s²
Accuracy	648 rad	Friction torque (at 20°C), max.	0.01 Nm
Sampling frequency, max.	300 kHz	Starting torque (at 20°C), max.	0.01 Nm
Switching time (10 ... 90 %)	= 200 ns  Rise / fall time t+/t- <=	Net weight	0.3 kg
		Max. admissible speed	
Phase relation signal A to B	90°	Electrical	180000 rpm
Edge clearance at 300 kHz	0.45 µs	Mechanical	12000 rpm
LED failure monitoring	High impedance driver	Load capacity	
Cable length		n <= 6000 rpm	
To the downstream electronics,	300 m	- Axial	40 N
Ambient temp in operation		- Radial at shaft end	60 N
		n > 6000 rpm	
Fixed installation of flange outlet or cable		- Axial	10 N
- At Up = 10V ... 30V	-40 ... 100 °C	- Radial at shaft end	20 N
Flexible cable		Shock, max.	
- At Up = 10V ... 30V	-10 ... 100 °C	2 ms	2000 m/s²
Standards		6 ms	1000 m/s²
		Degree of protection	
Compliance with standards	CE, cULus	Without shaft input	IP67
EMC class filter	Tested according to the EMC guidelines 89/336/EEC and the rules of the EMC guidelines (generic standards)	With shaft input	IP64