

MLFB-Ordering data 6FX2001-4HC50



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Electrical data		Mechanical data	
Operating voltage Up	DC 10 ... 30 V	Shaft diameter	6 mm
Max. power consumption without	150 mA	Shaft length	10 mm
Signal level	UH >= 21 V at IH = 20 mA at 24 V; UL <= 2,8 V at IL = 20 mA at 24 V	Angular acceleration, max.	100000 rad/s²
		Moment of inertia of rotor	0.00000145 kgm²
Resolution	2500 S/R	Vibration (55...2000 Hz), max.	300 m/s²
Accuracy	26 rad	Friction torque (at 20°C), max.	0.01 Nm
Sampling frequency, max.	300 kHz	Starting torque (at 20°C), max.	0.01 Nm
Switching time (10 ... 90 %)	= 200 ns	Net weight	0.3 kg
	Rise / fall time t+/t- <=	Max. admissible speed	
Phase relation signal A to B	90°	Electrical	7200 rpm
Edge clearance at 300 kHz	0.45 µs	Mechanical	12000 rpm
LED failure monitoring	High impedance driver	Load capacity	
Cable length		n <= 6000 rpm	
To the downstream electronics,	300 m	- Axial	40 N
Ambient temp in operation		- Radial at shaft end	60 N
Fixed installation of flange outlet or cable		n > 6000 rpm	
- At Up = 10V ... 30V	-40 ... 100 °C	- Axial	10 N
Flexible cable		- Radial at shaft end	20 N
- At Up = 10V ... 30V	-10 ... 100 °C	Shock, max.	
Standards		2 ms	2000 m/s²
Compliance with standards	CE, cULus	6 ms	1000 m/s²
EMC class filter	Tested according to the EMC guidelines 89/336/EEC and the rules of the EMC guidelines (generic standards)	Degree of protection	
		Without shaft input	IP67
		With shaft input	IP64