

MLFB-Ordering data

6FX2001-5WP12



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Electrical data		Mechanical data	
Operating voltage Up	DC 10 ... 30 V	Shaft version	Hollow shaft
Max. power consumption	100 ... 300 mA (2.5 W)	Shaft diameter	15 mm (8 mm / 10 mm / 12 mm with reducing sleeves)
Interface	PROFIBUS DP-V2	Angular acceleration, max.	100000 rad/s ²
Clock input	Differential line receiver according to EIA Standard RS 485	Moment of inertia of rotor	0.00000280 kgm ²
Data output	Differential line driver according to EIA Standard RS 485	Vibration (55...2000 Hz), max.	100 m/s ²
Short-circuit strength	Yes	Friction torque (at 20°C)	<= 0.01 Nm
Transmission rate	12 Mbit/s	Starting torque (at 20°C)	<= 0.01 Nm
LED for diagnostics	Yes (green/red)	Net weight	0.4 kg
Number of nodes	99	Speed max.	
Connection type	Terminal block with address selector switch and bus terminating resistor in removable cover with radial cable glands (3 units), Radial	With ± 1 bit accuracy	5800 rpm
Cable diameter	6.5 mm ... 9.0 mm, Tube dismantling possible without bus interruption	Max. permissible speed (mech.)	12000 rpm
Resolution	13 bit, (8192 increments)	Load capacity	
Telegram	According to PNO cncoder profile V4.1 Class1, Class 2, Class 3, standard telegram 81	n <= 6000 rpm	
Cable length up to the subsequent electronics, max.		- Axial	40 N
Up to 93.75 kbit/s	1200 m	- Radial at shaft end	110 N
Up to 1.5 Mbit/s	200.0 m	n > 6000 rpm	
Up to 12 Mbit/s	100.0 m	- Axial	10 N
Code type		- Radial at shaft end	20 N
Sampling	Gray	Shock, max.	
Transmission	binary, PROFIBUS	2 ms	2000 m/s ²
		6 ms	1000 m/s ²
		Degree of protection	
		Without shaft input	IP67
		With shaft input	IP64

MLFB-Ordering data

6FX2001-5WP12



Figure similar

Electrical data		Ambient temperature	
Parameterizability		During operation	-40 ... 85 °C
Preset	Yes	Standards	
Counting direction	Yes	Compliance with standards	CE, cULus
Resolution per revolution	Any 1 ... 8192	EMC class filter	Tested to DIN EN 50081 and EN 50082
Total resolution	Any 1 ... 8192		
Speed signal	Yes		
Limit switch	Yes, 2 pieces		
Clock synchronism	Yes		
Slave-to-slave communication	Yes		
Accuracy	± 79 " with 8192 increments (± 1/2 LSB)		