

MLFB-Ordering data                      6SL3100-0BE28-0AB0



Figure similar

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

Electrical data		General tech. specifications	
Input		Sound pressure level	68 dB
Number of phases	3 AC	Power loss	0.49 kW
Line voltage	380 ... 480 V	Ambient conditions	
Internal resistor	1440 Ω +10% -10%		
Rated data		Type of cooling	Internal air cooling
Rated current	128 A	Cooling air throughput	0.17 m³/s (5.90 ft³/s)
Power requirement (DC 24 V)	1.20 A	Standards	
Switching current (as NC circuit at 250 V AC)	1.6 A		
Switching current (as NC circuit at 60 V DC)	0.75 A	Compliance with standards	cURus
Mechanical data		Connections	
Dimensions		Line side	
Width	300 mm (11.81 in)	Version	M8 bolt
Height	380 mm (14.96 in)	Conductor cross-section	2.5 mm² ... 120 mm² (14 ... -3 AWG) (Alternatively 2 x 50 mm²)
Depth	270 mm (10.63 in)	PE conductor	M8 Screw
Degree of protection	IP20 / UL open type		
Net weight	31.90 kg (70.33 lb)		
Type of construction	Booksize		