



Figure similar

MLFB-Ordering data

6SL3210-5DE16-0UA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		Ambient conditions	
Input		Cooling	
Number of phases	3 AC	Forced-air cooling via fan	
Line voltage	380 ... 480 V -15 % +10 %	Installation altitude	
Line frequency	45 ... 66 Hz	Cooling air requirement	
Output		Ambient temperature	
Rated power	1.50 kW	Operation	
Rated current (IN)	4.60 A	Storage	
Max. output current	13.80 A	Transport	
Electronic power supply		Relative humidity	
Power supply	24 V ±10 %	Max. operation	
General tech. specifications		Standards	
Power loss	54.00 W	Compliance with standards	
Connections			
Motor end			
Conductor cross-section	2.5 mm²		
Mechanical data			
Degree of protection	IP20 / UL open type		
Frame size	FSB		
Net weight	2.45 kg (5.40 lb)		
Width	100.0 mm (3.94 in)		
Height	180.0 mm (7.09 in)		
Depth	200.0 mm (7.87 in)		