

SIEMENS

Data sheet for SINAMICS S210



Figure similar

MLFB-Ordering data 6SL3210-5HB10-8UF0

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data		Communication	
Input		Communication	PROFINET
Number of phases	1 AC	Ambient conditions	
Line voltage	200 ... 240 V ±10 %	Installation altitude	1000 m (3280.84 ft)
Line frequency	45 ... 66 Hz	Cooling	convection cooling
Rated current	9.3 A	Ambient temperature during	
Inrush current	8.0 A	Operation	0 ... 50 °C (32 ... 122 °F)
Output			Better than class 3K3, in acc. with EN 60721-3-3: 2002, without derating
Number of phases	3 AC	Transport	-40 ... 70 °C (-40 ... 158 °F)
Rated power	0.75 kW		Class 2K4, in acc. with EN 60721-3-2: 1997, in transport packaging
Rated current I _N	4.4 A	Storage	-25 ... 55 °C (-13 ... 131 °F)
Max. output current	16.0 A		Class 1K4, in acc. with EN 60721-3-1: 1997, in product packaging
Pulse frequency	8 kHz	Relative humidity during	
Output frequency for servo control	0 ... 550 Hz	Max. operation	95 %
Electronics power supply			RH, condensation not permitted
Voltage	24 V -15 % ... +20 %	Transport, max.	95 %
Current demand, max.	0.8 A		at 40 °C (104 °F)
		Bearing, max.	95 %



Figure similar

MLFB-Ordering data

6SL3210-5HB10-8UF0

Inputs / outputs	Connections																								
<div>Standard digital inputs</div> <table><tr><td>Number</td><td>5</td></tr><tr><td></td><td>of which 2 for F-DI</td></tr></table>	Number	5		of which 2 for F-DI	<div>Line side</div> <table><tr><td>Version</td><td>push-in spring-type terminals</td></tr><tr><td>Conductor cross-section</td><td>0.20 ... 2.50 mm² / 24 ... 14 AWG</td></tr></table>	Version	push-in spring-type terminals	Conductor cross-section	0.20 ... 2.50 mm² / 24 ... 14 AWG																
Number	5																								
	of which 2 for F-DI																								
Version	push-in spring-type terminals																								
Conductor cross-section	0.20 ... 2.50 mm² / 24 ... 14 AWG																								
<div>Fail-safe digital inputs</div> <table><tr><td>Number</td><td>1</td></tr><tr><td></td><td>Can only be used for STO/SS1</td></tr></table>	Number	1		Can only be used for STO/SS1	<div>Motor end</div> <table><tr><td>Version</td><td>push-in spring-type terminals</td></tr><tr><td>Conductor cross-section</td><td>0.20 ... 2.50 mm² / 24 ... 14 AWG</td></tr></table>	Version	push-in spring-type terminals	Conductor cross-section	0.20 ... 2.50 mm² / 24 ... 14 AWG																
Number	1																								
	Can only be used for STO/SS1																								
Version	push-in spring-type terminals																								
Conductor cross-section	0.20 ... 2.50 mm² / 24 ... 14 AWG																								
<div>Mechanical data</div> <div>Dimensions</div> <table><tr><td>Width</td><td>74.5 mm (2.93 in)</td></tr><tr><td>Height without shield plate</td><td>170.0 mm (6.69 in)</td></tr><tr><td>Depth</td><td>197.4 mm (7.77 in)</td></tr><tr><td>Mounting position</td><td>vertical wall mounting</td></tr><tr><td>Degree of protection</td><td>IP20 / UL open type</td></tr><tr><td>Frame size</td><td>FSC</td></tr><tr><td>Net weight</td><td>1.70 kg (3.75 lb)</td></tr></table>	Width	74.5 mm (2.93 in)	Height without shield plate	170.0 mm (6.69 in)	Depth	197.4 mm (7.77 in)	Mounting position	vertical wall mounting	Degree of protection	IP20 / UL open type	Frame size	FSC	Net weight	1.70 kg (3.75 lb)	<div>DC link (for braking resistor)</div> <table><tr><td>Version</td><td>push-in spring-type terminals</td></tr><tr><td>Conductor cross-section</td><td>0.20 ... 2.50 mm² / 24 ... 14 AWG</td></tr><tr><td>Cable length</td><td>3 m (9.84 ft)</td></tr></table> <div>PE connection</div> <table><tr><td>Version</td><td>M4 screw studs</td></tr></table> <div>Max. motor cable length ¹⁾</div> <table><tr><td>Shielded</td><td>50 m (164.04 ft)</td></tr></table>	Version	push-in spring-type terminals	Conductor cross-section	0.20 ... 2.50 mm² / 24 ... 14 AWG	Cable length	3 m (9.84 ft)	Version	M4 screw studs	Shielded	50 m (164.04 ft)
Width	74.5 mm (2.93 in)																								
Height without shield plate	170.0 mm (6.69 in)																								
Depth	197.4 mm (7.77 in)																								
Mounting position	vertical wall mounting																								
Degree of protection	IP20 / UL open type																								
Frame size	FSC																								
Net weight	1.70 kg (3.75 lb)																								
Version	push-in spring-type terminals																								
Conductor cross-section	0.20 ... 2.50 mm² / 24 ... 14 AWG																								
Cable length	3 m (9.84 ft)																								
Version	M4 screw studs																								
Shielded	50 m (164.04 ft)																								
<div>Standards</div> <table><tr><td>Compliance with standards</td><td>CE, cULus, RCM, KC, EAC, UKCA</td></tr><tr><td>CE marking</td><td>Low-voltage directive 2006/95/EC</td></tr><tr><td>Verification of suitability for fail-safety</td><td>SIL 2 in acc. with IEC 61508 parts 1-3 (2010) and IEC 61800-5-2 (2016), PL d in acc. with ISO 13849 part 1 (2015), Category 3 in acc. with ISO 13849 part 1 (2015)</td></tr></table>		Compliance with standards	CE, cULus, RCM, KC, EAC, UKCA	CE marking	Low-voltage directive 2006/95/EC	Verification of suitability for fail-safety	SIL 2 in acc. with IEC 61508 parts 1-3 (2010) and IEC 61800-5-2 (2016), PL d in acc. with ISO 13849 part 1 (2015), Category 3 in acc. with ISO 13849 part 1 (2015)																		
Compliance with standards	CE, cULus, RCM, KC, EAC, UKCA																								
CE marking	Low-voltage directive 2006/95/EC																								
Verification of suitability for fail-safety	SIL 2 in acc. with IEC 61508 parts 1-3 (2010) and IEC 61800-5-2 (2016), PL d in acc. with ISO 13849 part 1 (2015), Category 3 in acc. with ISO 13849 part 1 (2015)																								

¹⁾ Cable length with possibility of connection an external filter