

Article No. : 6SL3211-1PB13-8UL0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

| Rated data | | |
|---|---------------------|------------------------|
| Input | | |
| Number of phases | 1 / 3 AC | |
| Line voltage | 200 ... 240 V ±10 % | |
| Line frequency | 47 ... 63 Hz | |
| Rated current (LO) | 9.60 A / 5.50 A | |
| Rated current (HO) | 8.40 A / 4.80 A | |
| Output | | |
| Number of phases | 3 AC | |
| Rated voltage | 230V IEC | 240V NEC ¹⁾ |
| Rated power (LO) | 0.75 kW | 1.00 hp |
| Rated power (HO) | 0.55 kW | 0.75 hp |
| Rated current (LO) | 4.20 A | |
| Rated current (HO) | 3.20 A | |
| Max. output current | 6.40 A | |
| Pulse frequency | 4 kHz | |
| Output frequency for vector control | 0 ... 200 Hz | |
| Output frequency for V/f control | 0 ... 550 Hz | |
| Overload capability | | |
| Low Overload (LO) | | |
| 1.1 x rated output current (i.e. 110 % overload) for 57 s with a cycle time of 300 s 1.5 × rated output current (i.e. 150 % overload) for 3 s with a cycle time of 300 s | | |
| High Overload (HO) | | |
| 1.5 × output current rating (i.e., 150 % overload) for 57 s with a cycle time of 300 s 2 × output current rating (i.e., 200 % overload) for 3 s with a cycle time of 300 s | | |
| General tech. specifications | | |
| Power factor λ | 0.85 | |
| Offset factor cos φ | 0.95 | |
| Efficiency η | 0.96 | |
| Sound pressure level (1m) | 56 dB | |
| Power loss | 0.04 kW | |
| Filter class (integrated) | - | |

| Ambient conditions | |
|-------------------------|-------------------------------------|
| Cooling | Internal air cooling |
| Cooling air requirement | 0.005 m³/s (0.177 ft³/s) |
| Installation altitude | 1,000 m (3,280.84 ft) |
| Ambient temperature | |
| Operation LO | -5 ... 40 °C (23 ... 104 °F) |
| Operation HO | -5 ... 50 °C (23 ... 122 °F) |
| Transport | -25 ... 55 °C (-13 ... 131 °F) |
| Storage | -25 ... 55 °C (-13 ... 131 °F) |
| Relative humidity | |
| Max. operation | 95 % RH, condensation not permitted |

| Connections | |
|-------------------------|--|
| Line side | |
| Version | Plug-in screw terminals |
| Conductor cross-section | 1.00 ... 2.50 mm² (AWG 18 ... AWG 14) |
| Motor end | |
| Version | Plug-in screw terminals |
| Conductor cross-section | 1.00 ... 2.50 mm² (AWG 18 ... AWG 14) |
| Max. motor cable length | |
| Shielded | 50 m (164.04 ft) |
| Unshielded | 100 m (328.08 ft) |


| Mechanical data | |
|----------------------|---------------------|
| Degree of protection | IP20 / UL open type |
| Frame size | FSA |
| Net weight | 1.80 kg (3.97 lb) |
| Dimensions | |
| Width | 126 mm (4.96 in) |
| Height | 238 mm (9.37 in) |
| Depth | 171 mm (6.73 in) |

| Standards | |
|---------------------------|-------------------------------------|
| Compliance with standards | UL, cUL, CE, C-Tick (RCM), SEMI F47 |
| CE marking | Low-voltage directive 2006/95/EC |

Data sheet for SINAMICS Power module PM240-2 Push through

Article No. : 6SL3211-1PB13-8UL0

| Converter losses to IEC61800-9-2* | |
|--|---------|
| Efficiency class | IE2 |
| Comparison with the reference converter (90% / 100%) | 30.10 % |



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*calculated values

¹⁾The output current and HP ratings are valid for the voltage range 220V-240V