

Data sheet for SIMOTICS S-1FK7



Figure similar

MLFB-Ordering data

1FK7080-2AF71-1RA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Engineering data

Rated speed (100 K) 3000 rpm

Number of poles 8

Rated torque (100 K) 6.8 Nm

Rated current 4.4 A

Static torque (60 K) 6.60 Nm

Static torque (100 K) 8.0 Nm

Stall current (60 K) 4.00 A

Stall current (100 K) 4.90 A

Moment of inertia 14.200 kgcm²

Efficiency 92.0 %

Physical constants

Torque constant 1.61 Nm/A

Voltage constant at 20° C 105.0 V/1000*min⁻¹

Winding resistance at 20° C 0.98 Ω

Rotating field inductance 17.2 mH

Electrical time constant 17.50 ms

Mechanical time constant 1.52 ms

Thermal time constant 40 min

Shaft torsional stiffness 120000 Nm/rad

Net weight of the motor 10.3 kg

Mechanical data

Motor type Permanent-magnet synchronous motor

Motor type Compact

Shaft height 80

Cooling Natural cooling

Radial runout tolerance 0.050 mm

Concentricity tolerance 0.10 mm

Axial runout tolerance 0.10 mm

Vibration severity grade Grade A

Connector size 1

Degree of protection IP64

Design acc. to Code I IM B5 (IM V1, IM V3)

Temperature monitoring Pt1000 temperature sensor

Electrical connectors Connectors for signals and power rotatable

Color of the housing Standard (Anthracite RAL 7016)

Holding brake without holding brake

Shaft extension Feather key

Encoder system

Encoder AM20DQI: absolute encoder 20 bits (resolution 1048576, encoder-internal 512 S/R) + 12 bits multi-turn (traversing range 4096 revolutions)



Figure similar

MLFB-Ordering data

1FK7080-2AF71-1RA0

Optimum operating point		Recommended Motor Module	
Optimum speed	3000 rpm	Rated inverter current	5 A
Optimum power	2.1 kW	Maximum inverter current	15 A
Limiting data		Maximum torque	22.10 Nm
Max. permissible speed (mech.)	6000 rpm		
Max. permissible speed (inverter)	5500 rpm		
Maximum torque	25.0 Nm		
Maximum current	18.0 A		