

## Data sheet for SIMOTICS S-1FK7



Figure similar

MLFB-Ordering data

1FK7080-2AF71-1RB0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

| Engineering data                        |                          | Mechanical data             |                                    |                        |   |
|---|--------------------------|-----------------------------|------------------------------------|------------------------|---|
| Rated speed (100 K)                     | 3000 rpm                 | Motor type                  | Permanent-magnet synchronous motor |                        |   |
| Number of poles                         | 8                        | Motor type                  | Compact                            |                        |   |
| Rated torque (100 K)                    | 6.8 Nm                   | Shaft height                | 80                                 |                        |   |
| Rated current                           | 4.4 A                    | Cooling                     | Natural cooling                    |                        |   |
| Static torque (60 K)                    | 6.60 Nm                  | Radial runout tolerance     | 0.050 mm                           |                        |   |
| Static torque (100 K)                   | 8.00 Nm                  | Concentricity tolerance     | 0.10 mm                            |                        |   |
| Stall current (60 K)                    | 4.00 A                   | Axial runout tolerance      | 0.10 mm                            |                        |   |
| Stall current (100 K)                   | 4.90 A                   | Vibration severity grade    | Grade A                            |                        |   |
| Moment of inertia                       | 17.500 kgcm <sup>2</sup> | Connector size              | 1                                  |                        |   |
| Efficiency                              | 92.0 %                   | Degree of protection        | IP64                               |                        |   |
| <th colspan="2">Physical constants</th> |                          | Physical constants          |                                    | Design acc. to Code I  | IM B5 (IM V1, IM V3)  |
|   |                          | Torque constant             | 1.61 Nm/A                          | Temperature monitoring | Pt1000 temperature sensor   |
|   |                          | Voltage constant at 20° C   | 105.0 V/1000*min <sup>-1</sup>     | Electrical connectors  | Connectors for signals and power rotatable  |
|   |                          | Winding resistance at 20° C | 0.98 Ω                             | Color of the housing   | Standard (Anthracite RAL 7016)  |
|   |                          | Rotating field inductance   | 17.2 mH                            | Holding brake          | with holding brake  |
|   |                          | Electrical time constant    | 17.50 ms                           | Shaft end              | Feather key   |
|   |                          | Mechanical time constant    | 1.52 ms                            | Encoder system         | Encoder AM20DQI: absolute encoder 20 bits (resolution 1048576, encoder-internal 512 S/R) + 12 bits multi-turn (traversing range 4096 revolutions) |
|   |                          | Thermal time constant       | 40 min                             |                        |   |
|   |                          | Shaft torsional stiffness   | 81000 Nm/rad                       |                        |   |
|   |                          | Net weight of the motor     | 13.3 kg                            |                        |   |



Figure similar

MLFB-Ordering data

1FK7080-2AF71-1RB0

### Optimum operating point

|               |          |
|---------------|----------|
| Optimum speed | 3000 rpm |
| Optimum power | 2.1 kW   |

### Limiting data

|                                   |          |
|-----------------------------------|----------|
| Max. permissible speed (mech.)    | 6000 rpm |
| Max. permissible speed (inverter) | 5500 rpm |
| Maximum torque                    | 25.0 Nm  |
| Maximum current                   | 18.0 A   |

### Holding brake

|                       |                        |
|-----------------------|------------------------|
| Holding brake version | Permanent-magnet brake |
| Holding torque        | 22.0 Nm                |
| Power supply voltage  | DC 24 V $\pm$ 10 %     |
| Coil current          | 0.9 A                  |
| Opening time          | 200 ms                 |
| Closing time          | 60 ms                  |
| Highest braking work  | 1400 J                 |

### Recommended Motor Module

|                          |          |
|--------------------------|----------|
| Rated inverter current   | 5 A      |
| Maximum inverter current | 15 A     |
| Maximum torque           | 22.10 Nm |