

Data sheet for SIMOTICS S-1FK7



Figure similar

MLFB-Ordering data

1FK7084-3BF71-1BB2

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

| Engineering data | | Mechanical data | | | |
|---------------------------|---------------------------|-----------------------------|------------------------------------|------------------------|-------------------------------------------------------|
| Rated speed (100 K) | 3000 rpm | Motor type | Permanent-magnet synchronous motor | | |
| Number of poles | 8 | Motor type | High Inertia | | |
| Rated torque (100 K) | 10.0 Nm | Shaft height | 80 | | |
| Rated current | 6.5 A | Cooling | Natural cooling | | |
| Static torque (60 K) | 16.60 Nm | Radial runout tolerance | 0.050 mm | | |
| Static torque (100 K) | 20.0 Nm | Concentricity tolerance | 0.10 mm | | |
| Stall current (60 K) | 9.80 A | Axial runout tolerance | 0.10 mm | | |
| Stall current (100 K) | 12.10 A | Vibration severity grade | Grade A | | |
| Moment of inertia | 102.000 kgcm ² | Connector size | 1 | | |
| Efficiency | 93.0 % | Degree of protection | IP65 and DE flange IP67 | | |
| Physical constants | | Design acc. to Code I | IM B5 (IM V1, IM V3) | | |
| | | Torque constant | 1.66 Nm/A | Temperature monitoring | Pt1000 temperature sensor |
| | | Voltage constant at 20° C | 106.5 V/1000*min ⁻¹ | Electrical connectors | Connectors for signals and power rotatable |
| | | Winding resistance at 20° C | 0.28 Ω | Color of the housing | Standard (Anthracite RAL 7016) |
| | | Rotating field inductance | 5.9 mH | Holding brake | with holding brake |
| | | Electrical time constant | 21.00 ms | Shaft extension | Feather key |
| | | Mechanical time constant | 3.10 ms | Encoder system | Encoder AS24DQI: absolute encoder single-turn 24 bits |
| | | Thermal time constant | 55 min | | |
| | | Shaft torsional stiffness | 62000 Nm/rad | | |
| | | Net weight of the motor | 26.0 kg | | |



Figure similar

MLFB-Ordering data

1FK7084-3BF71-1BB2

Optimum operating point

| | |
|---------------|----------|
| Optimum speed | 2500 rpm |
| Optimum power | 3.2 kW |

Limiting data

| | |
|-----------------------------------|----------|
| Max. permissible speed (mech.) | 6000 rpm |
| Max. permissible speed (inverter) | 5400 rpm |
| Maximum torque | 61.0 Nm |
| Maximum current | 41.0 A |

Holding brake

| | |
|-----------------------|------------------------|
| Holding brake version | Permanent-magnet brake |
| Holding torque | 22.0 Nm |
| Power supply voltage | DC 24 V \pm 10 % |
| Coil current | 0.9 A |
| Opening time | 200 ms |
| Closing time | 60 ms |
| Highest braking work | 1400 J |

Recommended Motor Module

| | |
|--------------------------|----------|
| Rated inverter current | 18 A |
| Maximum inverter current | 54 A |
| Maximum torque | 61.00 Nm |