

Data sheet for SIMOTICS S-1FK7



Figure similar

MLFB-Ordering data

1FK7084-2AC71-1UH0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Engineering data		Mechanical data			
Rated speed (100 K)	2000 rpm	Motor type	Permanent-magnet synchronous motor		
Number of poles	8	Motor type	Compact		
Rated torque (100 K)	15.0 Nm	Shaft height	80		
Rated current	6.7 A	Cooling	Natural cooling		
Static torque (60 K)	16.60 Nm	Radial runout tolerance	0.050 mm		
Static torque (100 K)	20.00 Nm	Concentricity tolerance	0.10 mm		
Stall current (60 K)	6.90 A	Axial runout tolerance	0.10 mm		
Stall current (100 K)	8.50 A	Vibration severity grade	Grade A		
Moment of inertia	35.500 kgcm ²	Connector size	1		
Efficiency	93.0 %	Degree of protection	IP64		
<th colspan="2">Physical constants</th>		Physical constants		Design acc. to Code I	IM B5 (IM V1, IM V3)
		Torque constant	2.36 Nm/A	Temperature monitoring	Pt1000 temperature sensor
		Voltage constant at 20° C	152.0 V/1000*min ⁻¹	Electrical connectors	Connectors for signals and power rotatable
		Winding resistance at 20° C	0.58 Ω	Color of the housing	Standard (Anthracite RAL 7016)
		Rotating field inductance	12.0 mH	Holding brake	with holding brake
		Electrical time constant	20.50 ms	Shaft end	Plain shaft
		Mechanical time constant	1.02 ms	Encoder system	Resolver R15DQ: resolver 15 bits (resolution 32768, internal multi-pole)
		Thermal time constant	55 min		
		Shaft torsional stiffness	68000 Nm/rad		
		Net weight of the motor	21.3 kg		



Figure similar

MLFB-Ordering data

1FK7084-2AC71-1UH0

Optimum operating point

Optimum speed 2000 rpm

Optimum power 3.1 kW

Limiting data

Max. permissible speed (mech.) 6000 rpm

Max. permissible speed (inverter) 3800 rpm

Maximum torque 61.0 Nm

Maximum current 28.5 A

Holding brake

Holding brake version Permanent-magnet brake

Holding torque 22.0 Nm

Power supply voltage DC 24 V \pm 10 %

Coil current 0.9 A

Opening time 200 ms

Closing time 60 ms

Highest braking work 1400 J

Recommended Motor Module

Rated inverter current 9 A

Maximum inverter current 27 A

Maximum torque 58.40 Nm