

## Data sheet for SIMOTICS S-1FK7



Figure similar

MLFB-Ordering data

1FK7100-2AC71-1BH1

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Engineering data		Mechanical data			
Rated speed (100 K)	2000 rpm	Motor type	Permanent-magnet synchronous motor		
Number of poles	8	Motor type	Compact		
Rated torque (100 K)	14.5 Nm	Shaft height	100		
Rated current	7.1 A	Cooling	Natural cooling		
Static torque (60 K)	14.90 Nm	Radial runout tolerance	0.050 mm		
Static torque (100 K)	18.0 Nm	Concentricity tolerance	0.10 mm		
Stall current (60 K)	6.80 A	Axial runout tolerance	0.10 mm		
Stall current (100 K)	8.40 A	Vibration severity grade	Grade A		
Moment of inertia	62.000 kgcm <sup>2</sup>	Connector size	1		
Efficiency	92.0 %	Degree of protection	IP65		
<th colspan="2">Physical constants</th>		Physical constants		Design acc. to Code I	IM B5 (IM V1, IM V3)
		Torque constant	2.14 Nm/A	Temperature monitoring	Pt1000 temperature sensor
		Voltage constant at 20° C	138.0 V/1000*min <sup>-1</sup>	Electrical connectors	Connectors for signals and power rotatable
		Winding resistance at 20° C	0.55 Ω	Color of the housing	Standard (Anthracite RAL 7016)
		Rotating field inductance	12.7 mH	Holding brake	with holding brake
		Electrical time constant	23.00 ms	Shaft extension	Plain shaft
		Mechanical time constant	1.95 ms	Encoder system	Encoder AS24DQI: absolute encoder single-turn 24 bits
		Thermal time constant	55 min		
		Shaft torsional stiffness	135000 Nm/rad		
		Net weight of the motor	21.0 kg		



Figure similar

## MLFB-Ordering data

1FK7100-2AC71-1BH1

### Optimum operating point

Optimum speed	2000 rpm
Optimum power	3.0 kW

### Limiting data

Max. permissible speed (mech.)	5000 rpm
Max. permissible speed (inverter)	4200 rpm
Maximum torque	55.0 Nm
Maximum current	28.0 A

### Holding brake

Holding brake version	Permanent-magnet brake
Holding torque	23.0 Nm
Power supply voltage	DC 24 V $\pm$ 10 %
Coil current	1.0 A
Opening time	300 ms
Closing time	70 ms
Highest braking work	3380 J

### Recommended Motor Module

Rated inverter current	9 A
Maximum inverter current	27 A
Maximum torque	53.40 Nm