

## Data sheet for SIMOTICS S-1FK7



Figure similar

MLFB-Ordering data

1FK7105-2AC71-1QB0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

### Engineering data

Rated speed (100 K)	2000 rpm
Number of poles	8
Rated torque (100 K)	37.0 Nm
Rated current	16.0 A
Static torque (60 K)	40.00 Nm
Static torque (100 K)	48.0 Nm
Stall current (60 K)	16.20 A
Stall current (100 K)	20.00 A
Moment of inertia	162.000 kgcm <sup>2</sup>
Efficiency	93.0 %

### Physical constants

Torque constant	2.37 Nm/A
Voltage constant at 20° C	157.5 V/1000*min <sup>-1</sup>
Winding resistance at 20° C	0.17 Ω
Rotating field inductance	4.5 mH
Electrical time constant	25.50 ms
Mechanical time constant	1.40 ms
Thermal time constant	70 min
Shaft torsional stiffness	95000 Nm/rad
Net weight of the motor	43.5 kg

### Mechanical data

Motor type	Permanent-magnet synchronous motor
Motor type	Compact
Shaft height	100
Cooling	Natural cooling
Radial runout tolerance	0.050 mm
Concentricity tolerance	0.10 mm
Axial runout tolerance	0.10 mm
Vibration severity grade	Grade A
Connector size	1.5
Degree of protection	IP64
Design acc. to Code I	IM B5 (IM V1, IM V3)
Temperature monitoring	Pt1000 temperature sensor
Electrical connectors	Connectors for signals and power rotatable
Color of the housing	Standard (Anthracite RAL 7016)
Holding brake	with holding brake
Shaft extension	Feather key
Encoder system	Encoder AS20DQI: absolute encoder single-turn 20 bits



Figure similar

MLFB-Ordering data

1FK7105-2AC71-1QB0

### Optimum operating point

Optimum speed	2000 rpm
Optimum power	7.7 kW

### Limiting data

Max. permissible speed (mech.)	5000 rpm
Max. permissible speed (inverter)	3650 rpm
Maximum torque	150.0 Nm
Maximum current	71.0 A

### Holding brake

Holding brake version	Permanent-magnet brake
Holding torque	43.0 Nm
Power supply voltage	DC 24 V $\pm$ 10 %
Coil current	1.0 A
Opening time	300 ms
Closing time	70 ms
Highest braking work	3380 J

### Recommended Motor Module

Rated inverter current	30 A
Maximum inverter current	72 A
Maximum torque	150.00 Nm