



Figure similar

Article No. : 1FL6062-1AC61-2AH1

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Engineering data

| | |
|----------------------|--------------------------|
| Rated speed | 2,000 rpm |
| Rated torque (100 K) | 4.78 Nm |
| Rated current | 3.0 A |
| Rated power | 1.00 kW / 1.36 hp |
| Max. speed | 3,000 rpm |
| Maximum torque | 14.30 Nm |
| Max. current | 9 A |
| Static torque | 6.00 Nm |
| Moment of inertia | 13.500 kgcm ² |

Physical constants

| | |
|-----------------|------------|
| Torque constant | 1.70 Nm/A |
| Thermal class | B (130 °C) |
| Net weight | 10.10 kg |

Ambient conditions

| | |
|---------------------|--|
| Ambient temperature | |
| Operation | 0 ... 40 °C |
| Relative humidity | |
| Max. operation | 90 % RH maximum (no condensation at 30 °C) |

Standards

| | |
|---------------------------|---------|
| Compliance with standards | CE, EAC |
|---------------------------|---------|

Mechanical data

| | |
|--------------------------|--|
| Motor type | High Inertia |
| Motor type | Permanent-magnet synchronous motor |
| Shaft height | 65 |
| Encoder system | Incremental encoder TTL, 2500 S/R (13 bit) |
| Cooling | Natural cooling |
| Shaft end | Plain shaft |
| Radial runout tolerance | Class N |
| Vibration severity grade | Grade A |
| Degree of protection | IP65 |
| Design acc. to Code I | IM B5 (IM V1, IM V3) |
| Connection type | Angular connector (rotatable) |

Holding brake

| | |
|--------------------------|--------------|
| Holding torque M_{4Br} | 12.00 Nm |
| Rated voltage | 24 V DC 10 % |
| Opening time | 180 ms |
| Closing time | 60 ms |
| Rated current | 1.50 A |