


## Data sheet for three-phase Squirrel-Cage-Motors



MLFB-Ordering data : **1LA7063-4AB10**

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

### Electrical data:

Rated voltage :	(1) 230 VD/400 VY, 50 Hz, 460 VY, 60 Hz					
Frequency :	50 Hz		60 Hz			
Rated power :	0.18 kW		0.21 kW			
Rated speed :	1350 1/ min		1650 1/ min			
Rated torque :	1.3 Nm		1.2 Nm			
Rated current (IE) :	VD	VY	VY			
	1.01 A	0.58 A	0.59 A			
Starting / rated current :	3.0		3.1			
Breakdown / rated torque :	1.9		2.0			
Starting / rated torque :	1.9		2.0			
Efficiency %	4/4	3/4	2/4	4/4	3/4	2/4
	58.3%	56.8%	52.3%	58.3%	56.8%	52.3%
	0.76	0.70	0.59	0.77	0.71	0.59
Power factor :	0.76		0.77			
Efficiency class :	-/		-/			

### Mechanical data:

Sound pressure level 50Hz/60Hz (load) :	42 dB(A)	46 dB(A)
Moment of inertia :	0.00037 kg*m <sup>2</sup>	
Bearing DE :	6201 2ZC3	
Bearing NDE :	6201 2ZC3	
Type of bearing :	Floating bearings pre-loaded DE (standard)	
Condensate drainage holes :	No	
Regreasing device :	No	
Lubricants :	Esso Unirex N3	
Grease lifetime/Relubrication interval :	40000 h	
Quantity of grease for relubrication :	null g	
External earthing terminal :	No	
Coating :	Special paint finish RAL 7030 stone gray	

### Environmental conditions:

Ambient temperature :	-20 °C - +40 °C
Altitude above sea level :	1000 m
Standards and specifications :	IEC, DIN, ISO, VDE, EN

### General data:

Frame size	063 M
Design of electrical machine :	(0) IM B3 / B6 / B7 / B8 / V5 without canopy
Weight in kg, without optional accessories :	4.10 kg
Frame material :	Aluminum
Degree of protection :	IP 55
Method of cooling, TEFC :	IC 411
Vibration class :	A (Standard)
Insulation :	155(F) to 130(B)
Duty type :	S1 - continuous duty
Direction of rotation :	Bi-directional

### Terminal box:

Material of terminal box :	
Type of terminal box :	gk 030
Contact screw thread :	
Max. cross-sectional area :	
Cable diameter from ... to ... :	
Cable entry :	
Cable gland :	

### Special design: