

## Data sheet for three-phase Squirrel-Cage-Motors

MLFB-Ordering data : **1LA7096-2AA10**

Client order no. :  
Order no. :  
Offer no. :  
Remarks :

Item no. :  
Consignment no. :  
Project :

### Electrical data:

Rated voltage :	(1) 230 VD/400 VY, 50 Hz, 460 VY, 60 Hz					
Frequency :	50 Hz		60 Hz			
Rated power :	2.20 kW		2.55 kW			
Rated speed :	2880 1/ min		3480 1/ min			
Rated torque :	7.3 Nm		7.0 Nm			
Rated current (IE) :	VD	VY	VY			
	8.17 A	4.70 A	4.55 A			
Starting / rated current :	6.3		6.5			
Breakdown / rated torque :	3.1		3.1			
Starting / rated torque :	2.8		2.8			
	4/4	3/4	2/4	4/4	3/4	2/4
Efficiency %	79.7%	79.7%	78.7%	81.5%	81.5%	78.9%
Power factor :	0.85	0.81	0.73	0.86	0.83	0.75
Efficiency class :	IE1		IE1			

### Mechanical data:

Sound pressure level 50Hz/60Hz (load) :	60 dB(A)	64 dB(A)
Moment of inertia :	0.0018 kg*m <sup>2</sup>	
Bearing DE :	6205 2ZC3	
Bearing NDE :	6004 2ZC3	
Type of bearing :	Floating bearings pre-loaded DE (standard)	
Condensate drainage holes :	No	
Regreasing device :	No	
Lubricants :	Esso Unirex N3	
Grease lifetime/Relubrication interval :	40000 h	
Quantity of grease for relubrication :	null g	
External earthing terminal :	No	
Coating :	Special paint finish RAL 7030 stone gray	

### Environmental conditions:

Ambient temperature :	-20 °C - +40 °C
Altitude above sea level :	1000 m
Standards and specifications :	IEC, DIN, ISO, VDE, EN

### General data:

Frame size	090 L
Design of electrical machine :	(0) IM B3 / B6 / B7 / B8 / V5 without canopy
Weight in kg, without optional accessories :	15.70 kg
Frame material :	Aluminum
Degree of protection :	IP 55
Method of cooling, TEFC :	IC 411
Vibration class :	A (Standard)
Insulation :	155(F) to 130(B)
Duty type :	S1 - continuous duty
Direction of rotation :	Bi-directional

### Terminal box:

Material of terminal box :	
Type of terminal box :	gk 030
Contact screw thread :	
Max. cross-sectional area :	
Cable diameter from ... to ... :	
Cable entry :	
Cable gland :	

### Special design: