

Data sheet for three-phase Squirrel-Cage-Motors SIMOTICS



Motor type : 1AV1104A

SIMOTICS GP - 100 L - IM B3 - 2p

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	project

Remarks

Electrical data

Safe Area

U [V]	Δ / Y	f [Hz]	P [kW]	P [hp]	I [A]	n [1/min]	M [Nm]	η ³⁾			$\cos\phi$ ³⁾			I_A/I_N I_i/I_N	M_A/M_N T_i/T_N	M_k/M_N T_B/T_N	IE-CL
								4/4	3/4	2/4	4/4	3/4	2/4				
230	Δ	50	3.00	-/-	10.60	2835	10.1	81.5	83.2	82.7	0.87	0.82	0.73	6.4	3.2	3.5	IE1
400	Y	50	3.00	-/-	6.10	2835	10.1	81.5	83.2	82.7	0.87	0.82	0.73	6.4	3.2	3.5	IE1
460	Y	60	3.45	-/-	5.80	3435	9.6	84.5	85.5	85.2	0.88	0.84	0.75	7.4	3.9	3.9	IE1

IM B3 / IM 1001	FS 100 L	20 kg	IP55	IEC/EN 60034	IEC, DIN, ISO, VDE, EN
-----------------	----------	-------	------	--------------	------------------------

Environmental conditions : -20 °C - +40 °C / 1,000 m

Mechanical data

Sound level (SPL / SWL) at 50Hz 60Hz	67.0 / 79.0 dB(A) ²⁾	71.0 / 83.0 dB(A) ²⁾	External earthing terminal	No
Moment of inertia	0.0034 kg m ²		Vibration severity grade	A
Bearing DE NDE	6206 2Z C3	6206 2Z C3	Insulation	155(F) to 130(B)
bearing lifetime			Duty type	S1
L_{10mh} $F_{Rad, min}$ for coupling operation 50 60Hz ¹⁾	40000 h	32000 h	Direction of rotation	bidirectional
Lubricants	Unirex N3		Frame material	aluminum
Regreasing device	No		Coating (paint finish)	Standard paint finish C2
Grease nipple	-/-		Color, paint shade	RAL7030
Type of bearing	Preloaded bearing DE		Motor protection	(A) without (Standard)
Condensate drainage holes	No		Method of cooling	IC411 - self ventilated, surface cooled


Terminal box

Terminal box position	top	Max. cross-sectional area	4.0 mm ²
Material of terminal box	Aluminium	Cable diameter from ... to ...	11.0 mm - 21.0 mm
Type of terminal box	TB1 F00	Cable entry	2xM32x1,5
Contact screw thread	M4	Cable gland	2 plugs

Notes:

I_A/I_N = locked rotor current / current nominal	1) L10mh according to DIN ISO 281 10/2010	3) Value is valid only for DOL operation with motor design IC411
M_k/M_N = locked rotor torque / torque nominal	2) at rated power / at full load	
M_k/M_N = break down torque / nominal torque		

responsible dep. DI MC LVM	technical reference	created by DT Configurator	approved by	Technical data are subject to change! There may be discrepancies between calculated and rating plate values.
-------------------------------	---------------------	-------------------------------	-------------	--

	document type datasheet	document status released	customer	
	title 1LE1002-1AA42-2AA4	document number	rev. 01	creation date 2021-01-17 19:10
© Siemens AG 2021				Page 1/1