

Data sheet for three-phase Squirrel-Cage-Motors SIMOTICS



Motor type : 1AV1112B

SIMOTICS GP - 112 M - IM B14 - 4p

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	project
Remarks		

Electrical data

Safe Area

U [V]	Δ / Y	f [Hz]	P [kW]	P [hp]	I [A]	n [1/min]	M [Nm]	η ³⁾			$\cos\phi$ ³⁾			I_A/I_N I_i/I_N	M_A/M_N T_i/T_N	M_K/M_N T_B/T_N	IE-CL
								4/4	3/4	2/4	4/4	3/4	2/4				
230	Δ	50	4.00	-/-	14.60	1435	26.5	83.1	84.3	84.0	0.83	0.77	0.65	6.1	2.5	2.9	IE1
400	Y	50	4.00	-/-	8.40	1435	26.5	83.1	84.3	84.0	0.83	0.77	0.65	6.1	2.5	2.9	IE1
460	Y	60	4.55	-/-	8.10	1735	25.0	85.0	86.1	85.1	0.83	0.78	0.66	6.8	2.5	3.2	IE1

IM B14 / IM 3601	FS 112 M	27 kg	IP55	IEC/EN 60034	IEC, DIN, ISO, VDE, EN
Environmental conditions : -20 °C - +40 °C / 1,000 m					

Mechanical data

Sound level (SPL / SWL) at 50Hz 60Hz	58.0 / 70.0 dB(A) ²⁾	62.0 / 74.0 dB(A) ²⁾	External earthing terminal	No
Moment of inertia	0.0100 kg m ²		Vibration severity grade	A
Bearing DE NDE	6206 2Z C3	6206 2Z C3	Insulation	155(F) to 130(B)
bearing lifetime			Duty type	S1
L_{10mh} $F_{rad, min}$ for coupling operation 50 60Hz ¹⁾	40000 h	32000 h	Direction of rotation	bidirectional
Lubricants	Unirex N3		Frame material	aluminum
Regreasing device	No		Coating (paint finish)	Standard paint finish C2
Grease nipple	-/-		Color, paint shade	RAL7030
Type of bearing	Preloaded bearing DE		Motor protection	(A) without (Standard)
Condensate drainage holes	No		Method of cooling	IC411 - self ventilated, surface cooled

Terminal box

Terminal box position	top	Max. cross-sectional area	4.0 mm ²
Material of terminal box	Aluminium	Cable diameter from ... to ...	11.0 mm - 21.0 mm
Type of terminal box	TB1 F00	Cable entry	2xM32x1,5
Contact screw thread	M4	Cable gland	2 plugs

Notes:

I_A/I_N = locked rotor current / current nominal	1) L10mh according to DIN ISO 281 10/2010	3) Value is valid only for DOL operation with motor design IC411
M_L/M_N = locked rotor torque / torque nominal	2) at rated power / at full load	
M_K/M_N = break down torque / nominal torque		

responsible dep. DI MC LVM	technical reference	created by DT Configurator	approved by	<i>Technical data are subject to change! There may be discrepancies between calculated and rating plate values.</i>			
SIEMENS	document type datasheet	document status released		customer			
	title 1LE1002-1BB22-2KA4	document number					
© Siemens AG 2021	rev. 01	creation date 2021-01-17 19:39	language en	Page 1/1			