

Data sheet for three-phase Squirrel-Cage-Motors SIMOTICS



Motor type : 1AV1132C

SIMOTICS GP - 132 M - IM B5 - 6p

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	project

Remarks

Electrical data

Safe Area

U [V]	Δ / Y	f [Hz]	P [kW]	P [hp]	I [A]	n [1/min]	M [Nm]	η ³⁾			$\cos\phi$ ³⁾			I_A/I_N I_i/I_N	M_A/M_N T_i/T_N	M_K/M_N T_B/T_N	IE-CL
								4/4	3/4	2/4	4/4	3/4	2/4				
400	Δ	50	4.00	-/-	9.30	955	40.0	81.4	82.5	81.9	0.76	0.69	0.57	5.2	2.3	2.6	IE1
690	Y	50	4.00	-/-	5.40	955	40.0	81.4	82.5	81.9	0.76	0.69	0.57	5.2	2.3	2.6	IE1
460	Δ	60	4.55	-/-	8.90	1155	37.5	83.5	84.6	83.9	0.77	0.71	0.59	5.6	2.3	2.7	IE1

IM B5 / IM 3001	FS 132 M	39 kg	IP55	IEC/EN 60034	IEC, DIN, ISO, VDE, EN
-----------------	----------	-------	------	--------------	------------------------

Environmental conditions : -20 °C - +40 °C / 1,000 m

Mechanical data

Sound level (SPL / SWL) at 50Hz 60Hz	63.0 / 75.0 dB(A) ²⁾	67.0 / 79.0 dB(A) ²⁾	External earthing terminal	No
Moment of inertia	0.0210 kg m ²		Vibration severity grade	A
Bearing DE NDE	6208 2Z C3	6208 2Z C3	Insulation	155(F) to 130(B)
bearing lifetime			Duty type	S1
L _{10mh} F _{Rad min} for coupling operation 50 60Hz ¹⁾	40000 h	32000 h	Direction of rotation	bidirectional
Lubricants	Unirex N3		Frame material	aluminum
Regreasing device	No		Coating (paint finish)	Standard paint finish C2
Grease nipple	-/-		Color, paint shade	RAL7030
Type of bearing	Preloaded bearing DE		Motor protection	(A) without (Standard)
Condensate drainage holes	No		Method of cooling	IC411 - self ventilated, surface cooled


Terminal box

Terminal box position	top	Max. cross-sectional area	6.0 mm ²
Material of terminal box	Aluminium	Cable diameter from ... to ...	11.0 mm - 21.0 mm
Type of terminal box	TB1 H00	Cable entry	2xM32x1,5
Contact screw thread	M4	Cable gland	2 plugs

Notes:

I_A/I_N = locked rotor current / current nominal
 M_A/M_N = locked rotor torque / torque nominal
 M_K/M_N = break down torque / nominal torque
 1) L10mh according to DIN ISO 281 10/2010
 2) at rated power / at full load
 3) Value is valid only for DOL operation with motor design IC411

responsible dep. DI MC LVM	technical reference	created by DT Configurator	approved by	<i>Technical data are subject to change! There may be discrepancies between calculated and rating plate values.</i>
-------------------------------	---------------------	-------------------------------	-------------	---

	document type datasheet	document status released	customer	
	title 1LE1002-1CC23-4FA4	document number	rev. 01	creation date 2021-01-17 19:35
© Siemens AG 2021				Page 1/1