

Data sheet for three-phase Squirrel-Cage-Motors SIMOTICS



Motor type : 1CV1280B

SIMOTICS SD - 280 S - IM B3 - 4p

Client order no.	Item-No.	Offer no.
Order no.	Consignment no.	project
Remarks		

Electrical data

Safe Area

U [V]	Δ / Y	f [Hz]	P [kW]	P [hp]	I [A]	n [1/min]	M [Nm]	η ³⁾			$\cos\phi$ ³⁾			I_A/I_N I_i/I_N	M_A/M_N T_i/T_N	M_K/M_N T_B/T_N	IE-CL
								4/4	3/4	2/4	4/4	3/4	2/4				
400	Δ	50	75.00	-/-	137.00	1485	480.0	92.7	92.9	92.2	0.85	0.82	0.73	7.0	2.3	2.8	IE1
690	Y	50	75.00	-/-	80.00	1485	480.0	92.7	92.9	92.2	0.85	0.82	0.73	7.0	2.3	2.8	IE1
460	Δ	60	86.00	-/-	135.00	1785	460.0	93.2	93.2	92.4	0.86	0.83	0.76	7.0	2.3	2.8	IE1

IM B3 / IM 1001	FS 280 S	540 kg	IP55	IEC/EN 60034	IEC, DIN, ISO, VDE, EN
Environmental conditions : -20 °C - +40 °C / 1,000 m					

Mechanical data

Sound level (SPL / SWL) at 50Hz 60Hz	72.0 / 86.0 dB(A) ²⁾	76.0 / 90.0 dB(A) ²⁾	External earthing terminal	Yes (standard)
Moment of inertia	1.2000 kg m ²		Vibration severity grade	A
Bearing DE NDE	6317 C3	6317 C3	Insulation	155(F) to 130(B)
bearing lifetime			Duty type	S1
L _{10mh} F _{Rad min} for coupling operation 50 60Hz ¹⁾	40000 h	32000 h	Direction of rotation	bidirectional
Relubrication interval/quantity (AS BS)	30 g 30 g 8000 h		Frame material	cast iron
Lubricants	Unirex N3		Coating (paint finish)	Standard paint finish C2
Regreasing device	Yes (standard)		Color, paint shade	RAL7030
Grease nipple	M10x1 DIN 3404 A		Motor protection	(A) without (Standard)
Type of bearing	Locating bearing NDE		Method of cooling	IC411 - self ventilated, surface cooled
Condensate drainage holes	Yes (standard)			

Terminal box

Terminal box position	top	Max. cross-sectional area	120.0 mm ²
Material of terminal box	cast iron	Cable diameter from ... to ...	34.0 mm - 42.0 mm
Type of terminal box	TB1 N01	Cable entry	2xM63x1,5
Contact screw thread	M10	Cable gland	2 plugs

Notes:

I_A/I_N = locked rotor current / current nominal	1) L10mh according to DIN ISO 281 10/2010	3) Value is valid only for DOL operation with motor design IC411
M_A/M_N = locked rotor torque / torque nominal	2) at rated power / at full load	
M_K/M_N = break down torque / nominal torque		

responsible dep. DI MC LVM	technical reference	created by DT Configurator	approved by	<i>Technical data are subject to change! There may be discrepancies between calculated and rating plate values.</i>			
SIEMENS	document type datasheet	document status released		customer			
	title 1LE1502-2DB03-4AA4	document number					
© Siemens AG 2021	rev. 01	creation date 2021-01-17 20:39	language en	Page 1/1			