

SIEMENS

Data sheet for SIMOTICS M-1PH1



Figure similar

MLFB-Ordering data

1PH1103-1HF10-1GA0

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Engineering data

Rated power	5.5 kW
Rated speed	1500 rpm
Rated torque	35.0 Nm
Rated current	16.9 A
Rated voltage	290 V
Maximum speed	10000 rpm
Maximum current	33.8 A
Power for duty type S6-25%, maximum	8.25 kW
Standstill torque for duty type S6-25%, maximum	52.5 Nm
Standstill current for duty type S6-25%, maximum	24.0 A
Field weakening speed, max.	5500 rpm
Supply voltage, max.	355 V
Line frequency	53.0 Hz

Ambient conditions

Ambient temperature

Operation	-15 ... 40 °C
Storage	-20 ... 65 °C

Relative humidity

Max. operation	90 %
Bearing, max.	95 %

Mechanical data

Motor type	Squirrel cage asynchronous motor
Shaft height	100
Cooling	Forced-air cooling via fan
Vibration severity grade	Grade B
Degree of protection	IP54
Design acc. to Code I	IM B3 / IM V5
Color	Anthracite 614 / ~ RAL7016
Shaft extension	Feather key with full key balancing
Sound pressure level (1m)	72 dB
Thermal class	F
Mounting type	Foot-mounted
Encoder system	Absolute encoder single-turn (20 bit)