

MLFB-Ordering data

6FX2001-3CB00



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

### Electrical data

Operating voltage Up	DC 5 V ± 10 %
Max. power consumption without	150 mA
Signal level	Sinusoidal 1 Vpp
Resolution	1000 S/R
Accuracy	65 rad
Phase relation signal A to B	90° ± 10 %

### Limit frequency type at

-3 dB	≥ 100 kHz
-6 dB	≥ 200 kHz

### Cable length

To the downstream electronics,	150 m
--------------------------------	-------

### Ambient temp in operation

#### Fixed installation of flange outlet or cable

- At Up = 5V ± 10%	-40 ... 100 °C
--------------------	----------------

#### Flexible cable

- At Up = 5V ± 10%	-10 ... 100 °C
--------------------	----------------

### Standards

Compliance with standards	CE, cULus
EMC class filter	Tested according to the EMC guidelines 89/336/EEC and the rules of the EMC guidelines (generic standards)

### Mechanical data

Shaft diameter	6 mm
Shaft length	10 mm
Angular acceleration, max.	100000 rad/s <sup>2</sup>
Moment of inertia of rotor	0.00000145 kgm <sup>2</sup>
Vibration (55...2000 Hz), max.	300
Friction torque (at 20°C), max.	0.01 Nm
Starting torque (at 20°C), max.	0.01 Nm

Net weight 0.3 kg

### Max. admissible speed

Electrical	18000 rpm
Mechanical	12000 rpm

### Load capacity

n = 6000 rpm	
- Axial	10 N
- Radial at shaft end	20 N

n > 6000 rpm	
- Axial	40 N
- Radial at shaft end	60 N

### Shock, max.

2 ms	2000 m/s <sup>2</sup>
6 ms	1000 m/s <sup>2</sup>

### Degree of protection

Without shaft input	IP67
With shaft input	IP64