

MOTION CONNECT 500

MLFB-Ordering data

6FX5002-2DC36-1CA0



Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Electrical data

| | |
|---|--------------------------|
| Design of the sensor | Motor encoder DRIVE-CLiQ |
| Test voltage, rms Signal conductors | 500 V |
| Rated voltage U0/U in accordance with EN 50395 Power conductors | 30 V |

Mechanical data

| | |
|---|----------------------|
| Type of connection cable engine side | M12 full thread |
| Type of connection cable converter side | DRIVE-CLiQ RJ45 |
| Maximum cable outer diameter | 7.1 mm |
| Smallest bending radius (fixed installation) | 35 mm |
| Smallest bending radius (flexible installation) | 125 mm |
| Number of bends, max. | 100,000 |
| Maximum traversing velocity | 30 m/min |
| Acceleration horizontal, max | 2 m/s ² |
| Tensile stress, max. Fixed installation | 80 N/mm ² |
| Tensile stress, max. Flexible installation | 30 N/mm ² |
| Torsional stress | Absolute 30°/m |
| Length | 20.0 m |



Figure similar

MLFB-Ordering data

6FX5002-2DC36-1CA0

Technical data

Ambient temperature

| | |
|---|---------------------------------|
| Operation with permanently installed cable | -20 ... 80 °C |
| Operation with moving cable | 0 ... 60 °C |
| Storage | -20 ... 80 °C |
| Kind of connection cable | Basis cable |
| Material of the cable sheath | PVC DESINA-Color green RAL 6018 |
| Type of insulation | Without CFC and silicone |
| Standard for behavior in fire: flame resistance | EN 60332-1-1 to 1-3 |
| Oil resistance | EN 60811-2-1 (mineral oil only) |
| Verification of suitability as authorisation for USA | UL STYLE 2502 |
| Verification of suitability as authorisation for Canada | CSA-N.210.2-M90 |