

MLFB-Ordering data

6SL3210-5BE27-5UV0

Figure similar

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

### Rated data

#### Input

Number of phases	3 AC
Line voltage	380 ... 480 V -15 % +10 %
Line frequency	47 ... 63 Hz

#### Output

Number of phases	3 AC
Rated voltage	400 V
Rated power (HO)	7.50 kW / 10.00 hp
Rated power (LO)	7.50 kW / 10.00 hp
Rated current (HO)	16.50 A
Rated current (LO)	16.50 A
Rated current (HO) at 480V	16.50 A
Rated current (LO) at 480V	16.50 A
Pulse frequency	4.00 kHz
Output frequency	0 ... 550 Hz

### General tech. specifications

Power factor $\lambda$	0.72
Offset factor $\cos \varphi$	0.95
Efficiency $\eta$	0.98
Filter class (integrated)	Unfiltered

### Ambient conditions

Cooling	External fan
Installation altitude	1000 m (3281 ft)

#### Ambient temperature

Operation	-10 ... 60 °C (14 ... 140 °F)
Storage	-40 ... 70 °C (-40 ... 158 °F)

#### Relative humidity

Max. operation	95 %
----------------	------

### Communication

Communication	USS, Modbus RTU
---------------	-----------------

### Standards

Compliance with standards	CE, cULus, C-Tick (RCM), KC
CE marking	EN 61800-5-1 /EN 60204-1 and EN 61800-3

### Overload capability

#### Low Overload (LO)

110 % rated output current for 60 s, cycle time 300 s

#### High Overload (HO)

150 % rated output current for 60 s, cycle time 300 s

MLFB-Ordering data

6SL3210-5BE27-5UV0

Figure similar

### Mechanical data

Mounting position	Through-hole mounting / wall mounting / side-by-side mounting
Degree of protection	IP20 / UL open type
Size	FSD
Net weight	3.70 kg ( 8.16 lb )
Width	240.0 mm ( 9.45 in )
Height	206.5 mm ( 8.13 in )
Depth	172.5 mm ( 6.79 in )

### Connections

#### Max. motor cable length

Shielded	25 m (82 ft)
Unshielded	50 m (164 ft)

### Inputs / outputs

#### Standard digital inputs

Number	4
--------	---

#### Digital outputs

Number as relay changeover contact	1
Number as transistor	1

#### Analog inputs

Number	2 (Can be used as additional digital input)
--------	---

#### Analog outputs

Number	1
--------	---