



Figure similar

### MLFB-Ordering data

6SL3210-1KE32-1AF1

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data		General tech. specifications	
<b>Input</b>		<b>Power factor <math>\lambda</math></b>	0.90 ... 0.95
Number of phases	3 AC	<b>Offset factor <math>\cos \phi</math></b>	0.99
Line voltage	380 ... 480 V +10 % -20 %	<b>Efficiency <math>\eta</math></b>	0.99
Line frequency	47 ... 63 Hz	<b>Sound pressure level (1m)</b>	68 dB
Rated current (LO)	187.00 A	<b>Power loss</b>	1.83 kW
Rated current (HO)	169.00 A	<b>Filter class (integrated)</b>	Class A
<b>Output</b>		<b>Ambient conditions</b>	
Number of phases	3 AC	<b>Cooling</b>	Air cooling using an integrated fan
Rated voltage	400 V	<b>Cooling air requirement</b>	0.153 m <sup>3</sup> /s (5.403 ft <sup>3</sup> /s)
Rated power IEC 400V (LO)	110.00 kW	<b>Installation altitude</b>	1000 m (3280.84 ft)
Rated power NEC 480V (LO)	125.00 hp	<b>Ambient temperature</b>	
Rated power IEC 400V (HO)	90.00 kW	<b>Operation</b>	-20 ... 40 °C (-4 ... 104 °F)
Rated power NEC 480V (HO)	100.00 hp	<b>Transport</b>	-40 ... 70 °C (-40 ... 158 °F)
Rated current (IN)	201.00 A	<b>Storage</b>	-40 ... 70 °C (-40 ... 158 °F)
Rated current (LO)	201.00 A	<b>Relative humidity</b>	
Rated current (HO)	164.00 A	<b>Max. operation</b>	95 % RH, condensation not permitted
Max. output current	328.00 A	<b>Closed-loop control techniques</b>	
Pulse frequency	2 kHz	<b>V/f linear / square-law / parameterizable</b>	Yes
Output frequency for vector control	0 ... 240 Hz	<b>V/f with flux current control (FCC)</b>	Yes
Output frequency for V/f control	0 ... 550 Hz	<b>V/f ECO linear / square-law</b>	Yes
<b>Overload capability</b>		<b>Sensorless vector control</b>	Yes
<b>Low Overload (LO)</b>	150 % base load current IL for 3 s, followed by 110 % base load current IL for 57 s in a 300 s cycle time	<b>Vector control, with sensor</b>	No
<b>High Overload (HO)</b>	200 % base load current IH for 3 s, followed by 150 % base load current IH for 57 s in a 300 s cycle time	<b>Encoderless torque control</b>	No
		<b>Torque control, with encoder</b>	No



Figure similar

### MLFB-Ordering data

6SL3210-1KE32-1AF1

#### Mechanical data

Degree of protection	IP20 / UL open type
Size	FSF
Net weight	65.50 kg (144.40 lb)
Width	305 mm (12.01 in)
Height	708 mm (27.87 in)
Depth	357 mm (14.06 in)

#### Inputs / outputs

##### Standard digital inputs

Number	6
Switching level: 0→1	11 V
Switching level: 1→0	5 V
Max. inrush current	15 mA

##### Fail-safe digital inputs

Number	1
--------	---

##### Digital outputs

Number as relay changeover contact	1
Output (resistive load)	DC 30 V, 0.5 A
Number as transistor	1
Output (resistive load)	DC 30 V, 0.5 A

##### Analog / digital inputs

Number	1 (Differential input)
Resolution	10 bit

##### Switching threshold as digital input

0→1	4 V
1→0	1.6 V

##### Analog outputs

Number	1 (Non-isolated output)
--------	-------------------------

##### PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected: PTC, KTY and Thermo-Click, accuracy ±5 °C

#### Communication

Communication	PROFINET, EtherNet/IP
---------------	-----------------------

#### Connections

##### Signal cable

Conductor cross-section	0.15 ... 1.50 mm <sup>2</sup> (AWG 24 ... AWG 16)
-------------------------	---

##### Line side

Version	screw-type terminal
Conductor cross-section	35.00 ... 120.00 mm <sup>2</sup> (AWG 2 ... AWG -3)

##### Motor end

Version	Screw-type terminals
Conductor cross-section	35.00 ... 120.00 mm <sup>2</sup> (AWG 2 ... AWG -3)

##### DC link (for braking resistor)

Version	Screw-type terminals
Conductor cross-section	35.00 ... 120.00 mm <sup>2</sup> (AWG 2 ... AWG -3)
Line length, max.	10 m (32.81 ft)
PE connection	Screw-type terminals

##### Max. motor cable length

Shielded	300 m (984.25 ft)
Unshielded	450 m (1476.38 ft)

#### Standards

Compliance with standards	UL, cUL, CE, C-Tick (RCM)
CE marking	EMC Directive 2004/108/EC, Low-Voltage Directive 2006/95/EC




Figure similar

MLFB-Ordering data

6SL3210-1KE32-1AF1

### Converter losses to EN 50598-2\*

Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	-0.41 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard EN 50598) of the relative torque generating current (I) over the relative motor stator frequency(f). The values are valid for the basic version of the converter without options/components.

\*converted values