



Figure similar

MLFB-Ordering data

6SL3210-5BB12-5UV1

Client order no. :

Order no. :

Offer no. :

Remarks :

Item no. :

Consignment no. :

Project :

Rated data	General tech. specifications																														
Input <table border="1"> <tr> <td>Number of phases</td> <td>1 AC</td> </tr> <tr> <td>Line voltage</td> <td>200 ... 240 V -15 % +10 %</td> </tr> <tr> <td>Line frequency</td> <td>47 ... 63 Hz</td> </tr> </table>	Number of phases	1 AC	Line voltage	200 ... 240 V -15 % +10 %	Line frequency	47 ... 63 Hz	<table border="1"> <tr> <td>Power factor λ</td> <td>0.72</td> </tr> <tr> <td>Offset factor $\cos \varphi$</td> <td>0.95</td> </tr> <tr> <td>Efficiency η</td> <td>0.98</td> </tr> <tr> <td>Filter class (integrated)</td> <td>Unfiltered</td> </tr> </table>	Power factor λ	0.72	Offset factor $\cos \varphi$	0.95	Efficiency η	0.98	Filter class (integrated)	Unfiltered																
Number of phases	1 AC																														
Line voltage	200 ... 240 V -15 % +10 %																														
Line frequency	47 ... 63 Hz																														
Power factor λ	0.72																														
Offset factor $\cos \varphi$	0.95																														
Efficiency η	0.98																														
Filter class (integrated)	Unfiltered																														
Output <table border="1"> <tr> <td>Number of phases</td> <td>3 AC</td> </tr> <tr> <td>Rated voltage</td> <td>230 V</td> </tr> <tr> <td>Rated power (HO)</td> <td>0.25 kW / 0.33 hp</td> </tr> <tr> <td>Rated power (LO)</td> <td>0.25 kW / 0.25 hp</td> </tr> <tr> <td>Rated current (HO)</td> <td>1.70 A</td> </tr> <tr> <td>Rated current (LO)</td> <td>1.70 A</td> </tr> <tr> <td>Pulse frequency</td> <td>8.00 kHz</td> </tr> <tr> <td>Output frequency</td> <td>0 ... 550 Hz</td> </tr> </table>	Number of phases	3 AC	Rated voltage	230 V	Rated power (HO)	0.25 kW / 0.33 hp	Rated power (LO)	0.25 kW / 0.25 hp	Rated current (HO)	1.70 A	Rated current (LO)	1.70 A	Pulse frequency	8.00 kHz	Output frequency	0 ... 550 Hz	Ambient conditions <table border="1"> <tr> <td>Cooling</td> <td>convection cooling</td> </tr> <tr> <td>Installation altitude</td> <td>1000 m (3281 ft)</td> </tr> <tr> <td>Ambient temperature</td> <td></td> </tr> <tr> <td>Operation</td> <td>-10 ... 60 °C (14 ... 140 °F)</td> </tr> <tr> <td>Storage</td> <td>-40 ... 70 °C (-40 ... 158 °F)</td> </tr> <tr> <td>Relative humidity</td> <td></td> </tr> <tr> <td>Max. operation</td> <td>95 %</td> </tr> </table>	Cooling	convection cooling	Installation altitude	1000 m (3281 ft)	Ambient temperature		Operation	-10 ... 60 °C (14 ... 140 °F)	Storage	-40 ... 70 °C (-40 ... 158 °F)	Relative humidity		Max. operation	95 %
Number of phases	3 AC																														
Rated voltage	230 V																														
Rated power (HO)	0.25 kW / 0.33 hp																														
Rated power (LO)	0.25 kW / 0.25 hp																														
Rated current (HO)	1.70 A																														
Rated current (LO)	1.70 A																														
Pulse frequency	8.00 kHz																														
Output frequency	0 ... 550 Hz																														
Cooling	convection cooling																														
Installation altitude	1000 m (3281 ft)																														
Ambient temperature																															
Operation	-10 ... 60 °C (14 ... 140 °F)																														
Storage	-40 ... 70 °C (-40 ... 158 °F)																														
Relative humidity																															
Max. operation	95 %																														
	Communication <table border="1"> <tr> <td>Communication</td> <td>USS, Modbus RTU</td> </tr> </table>	Communication	USS, Modbus RTU																												
Communication	USS, Modbus RTU																														
	Standards <table border="1"> <tr> <td>Compliance with standards</td> <td>CE, cULus, C-Tick (RCM), KC</td> </tr> <tr> <td>CE marking</td> <td>EN 61800-5-1 / EN 60204-1 and EN 61800-3</td> </tr> </table>	Compliance with standards	CE, cULus, C-Tick (RCM), KC	CE marking	EN 61800-5-1 / EN 60204-1 and EN 61800-3																										
Compliance with standards	CE, cULus, C-Tick (RCM), KC																														
CE marking	EN 61800-5-1 / EN 60204-1 and EN 61800-3																														

Overload capability

Low Overload (LO)

110 % rated output current for 60 s, cycle time 300 s

High Overload (HO)

150 % rated output current for 60 s, cycle time 300 s



Figure similar

MLFB-Ordering data

6SL3210-5BB12-5UV1

Mechanical data

Mounting position	Wall mounting / side-by-side mounting
Degree of protection	IP20 / UL open type
Size	F5AA
Net weight	0.70 kg (1.54 lb)
Width	68.0 mm (2.68 in)
Height	142.0 mm (5.59 in)
Depth	107.8 mm (4.24 in)

Inputs / outputs

Standard digital inputs

Number	4
--------	---

Digital outputs

Number as relay changeover contact	1
Number as transistor	1

Analog inputs

Number	2 (Can be used as additional digital input)
--------	---

Analog outputs

Number	1
--------	---

Connections

Max. motor cable length

Shielded	25 m (82 ft)
Unshielded	50 m (164 ft)