

Data sheet for SINAMICS G120P Cabinet



MLFB-Ordering data: 6SL3710-1PG34-0AA0 **

Client order no.:
Order no.:
Offer no.:
Remarks:

Item no.:
Consignment no.:
Project:

Rated data

Input

Supply frequency	47...63 Hz
Supply voltage	690 V ±10%
Rated input current	408.0 A
Max. current	550 A
Pulse number	6
Energy recovery capability	No (2Q)

Output:

Output voltage	690 V
Rated power (LO) in kW	355 kW
Rated power (HO) in kW	315 kW
Rated output current ***	393.0 A
Rated output current (LO) ***	385 A
Rated output current (HO) ***	314 A
Output current Max	529 A
Pulse frequency (nominal)	2.00 kHz

Basic data:


Absolute power loss in stand-by	232 W
Sound pressure level L_{pA} (1 m)	69 dB
Conductor cross section, max. (IEC)	4 x 240 mm ²
Degree of protection	IP20
Installation envelope dimensions (H x W x D)	2300 mm x 1200 mm x 600 mm
Weight approx.	522 kg
Frame size	FSHX
Design	A
Color, paint shade	RAL7035
Compliance with standards	CE, RCM, EAC

Environmental conditions

Installation altitude	1000 m
Coolant	Air
Coolant requirement, air	0.60 m ³ /s
Ambient temperature	0 °C - +40 °C

Converter losses to IEC61800-9-2*

Efficiency class IE2
Comparison with the reference converter (90% / 100%) 37.8 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter including line choke without options/components.

Special design

*calculated values

**EMC shield rail with PE rail and crane transport aid included in the standard scope of delivery

***reduced value due to derating