

SIEMENS



Product overview for SIMATIC S7-1200

TIA Selection Tool Web



Basic Controller SIMATIC S7-1200

Flexibly adaptable to your requirements

SIMATIC S7-1200 controllers are the intelligent choice for compact automation solutions with integrated I/Os, communication and technology functions for automation tasks in the low to medium performance range. They are available in standard and fail-safe versions.

<https://www.siemens.com/s7-1200>

System overview

The scalable SIMATIC S7-1200 controllers have integrated inputs and outputs as well as communication options and are modularly expandable. Digital and analog input and output modules as well as a wide variety of communication modules enable flexible adaptation to the respective automation task. With integrated technologies such as high-speed counters, pulse width modulation, pulse sequence outputs, speed control and positioning, SIMATIC S7-1200 controllers are suitable for temperature control, pump and fan control, conveyor technology and even packaging machines.

Efficient engineering

- The seamless integration of the SIMATIC controllers into the common engineering framework TIA Portal provides consistent data management, the smart library concept and a uniform operating philosophy. This makes it especially easy to use system-spanning functions.

Manifold diagnostics

- Efficient error analysis and fast error localization with the new uniform display concept – plain text information of the error message in TIA Portal, on the HMI and in the Web server – shortens commissioning times and minimizes production downtimes. SIMATIC S7-1200 offers you diagnostic functionality already integrated in the system without additional programming work.

Innovative design

- The SIMATIC S7-1200 Basic Controller can be perfectly adapted to the respective automation task by implementing a wide range of expansion options. The modular board concept allows the controller to be easily expanded without changing its physical size. Devices can be easily replaced without rewiring by employing terminal strips.

Safety Integrated

- Fail-safe automation is as easy to program as the standard, and PROFIsafe devices are connected via PROFINET.

Technology Integrated

- Simple Motion Control applications, fast counting and measuring tasks, and closed-loop control (PID) are possible without special expansion modules.

Security Integrated

- Secure communication, know-how protection, copy protection and access protection prevent manipulation, opening and duplication of blocks by unauthorized persons, thus protecting your algorithm or process.

Five steps to the right controller:

Type of structure, system performance, programming, Motion Control, system architecture: Do you already know which functions and performance features your controller should have? Then our function check will take you directly to the right SIMATIC controller in five steps.

<https://www.siemens.com/controller>

Central processing units




	Article number
CPU 1211C	
CPU 1211C, DC/DC/DC, 6DI/4DO/2AI	6ES7211-1AE40-0XB0
CPU 1211C, AC/DC/Relay, 6DI/4DO/2AI	6ES7211-1BE40-0XB0
CPU 1211C, DC/DC/Relay, 6DI/4DO/2AI	6ES7211-1HE40-0XB0
CPU 1212C	
CPU 1212C ,DC/DC/DC, 8DI/6DO/2AI	6ES7212-1AE40-0XB0
CPU 1212C, AC/DC/Relay, 8DI/6DO/2AI	6ES7212-1BE40-0XB0
CPU 1212C, DC/DC/Relay, 8DI/6DO/2AI	6ES7212-1HE40-0XB0
CPU 1212FC ,DC/DC/DC, 8DI/6DO/2AI	6ES7212-1AF40-0XB0
CPU 1212FC, DC/DC/Relay, 8DI/6DO/2AI	6ES7212-1HF40-0XB0
SIPLUS S7-1200 CPU 1212 AC/DC/RLY	6AG1212-1BE40-2XB0
SIPLUS S7-1200 CPU 1212 AC/DC/RLY	6AG1212-1BE40-4XB0
SIPLUS S7-1200 CPU 1212C DC/DC/DC RAIL	6AG2212-1AE40-1XB0
SIPLUS S7-1200 CPU 1212 DC/DC/DC	6AG1212-1AE40-2XB0
SIPLUS S7-1200 CPU 1212 DC/DC/DC	6AG1212-1AE40-4XB0
SIPLUS S7-1200 CPU 1212 DC/DC/RLY	6AG1212-1HE40-4XB0
SIPLUS S7-1200 CPU 1212 DC/DC/RLY	6AG1212-1HE40-2XB0
CPU 1214C	
CPU 1214C, DC/DC/DC, 14DI/10DO/2AI	6ES7214-1AG40-0XB0
CPU 1214C, AC/DC/Relay, 14DI/10DO/2AI	6ES7214-1BG40-0XB0
CPU 1214C, DC/DC/Relay, 14DI/10DO/2AI	6ES7214-1HG40-0XB0
CPU 1214 FC, DC/DC/DC, 14DI/10DO/2AI	6ES7214-1AF40-0XB0
CPU 1214 FC, DC/DC/Relay, 14DI/10DO/2AI	6ES7214-1HF40-0XB0
SIPLUS S7-1200 CPU 1214 AC/DC/RLY	6AG1214-1BG40-4XB0
SIPLUS S7-1200 CPU 1214 AC/DC/RLY	6AG1214-1BG40-5XB0
SIPLUS S7-1200 CPU 1214 AC/DC/RLY	6AG1214-1BG40-2XB0
SIPLUS S7-1200 CPU 1214C DC/DC/DC RAIL	6AG2214-1AG40-1XB0
SIPLUS S7-1200 CPU 1214 DC/DC/DC	6AG1214-1AG40-4XB0
SIPLUS S7-1200 CPU 1214 DC/DC/DC	6AG1214-1AG40-5XB0
SIPLUS S7-1200 CPU 1214 DC/DC/DC	6AG1214-1AG40-2XB0
SIPLUS S7-1200 CPU 1214 DC/DC/RLY	6AG1214-1HG40-2XB0
SIPLUS S7-1200 CPU 1214 DC/DC/RLY	6AG1214-1HG40-4XB0
SIPLUS S7-1200 CPU 1214 DC/DC/RLY	6AG1214-1HG40-5XB0
SIPLUS S7-1200 CPU 1214FC DC/DC/DC	6AG1214-1AF40-5XB0
SIPLUS S7-1200 CPU 1214FC DC/DC/RLY	6AG1214-1HF40-5XB0
CPU 1215C	
CPU 1215C, DC/DC/DC, 14DI/10DO/2AI/2AO	6ES7215-1AG40-0XB0
CPU 1215C, AC/DC/RLY, 14DI/10DO/2AI/2AO	6ES7215-1BG40-0XB0
CPU 1215C, DC/DC/RLY, 14DI/10DO/2AI/2AO	6ES7215-1HG40-0XB0
CPU 1215 FC, DC/DC/DC, 14DI/10DO/2AI/2AO	6ES7215-1AF40-0XB0
CPU 1215 FC, DC/DC/RLY, 14DI/10DO/2AI/2AO	6ES7215-1HF40-0XB0
SIPLUS S7-1200 CPU 1215 AC/DC/RLY	6AG1215-1BG40-4XB0
SIPLUS S7-1200 CPU 1215 AC/DC/RLY	6AG1215-1BG40-2XB0
SIPLUS S7-1200 CPU 1215C AC/DC/RLY	6AG1215-1BG40-5XB0
SIPLUS S7-1200 CPU 1215C DC/DC/DC	6AG1215-1AG40-5XB0
SIPLUS S7-1200 CPU 1215C DC/DC/RLY	6AG1215-1HG40-5XB0
SIPLUS S7-1200 CPU 1215 DC/DC/DC	6AG1215-1AG40-4XB0
SIPLUS S7-1200 CPU 1215 DC/DC/DC	6AG1215-1AG40-2XB0
SIPLUS S7-1200 CPU 1215 DC/DC/RLY	6AG1215-1HG40-2XB0
SIPLUS S7-1200 CPU 1215 DC/DC/RLY	6AG1215-1HG40-4XB0
SIPLUS S7-1200 CPU 1215FC DC/DC/DC	6AG1215-1AF40-5XB0
CPU 1217C	
CPU 1217C, DC/DC/DC, 14DI/10DQ/2AI/2AQ	6ES7217-1AG40-0XB0


: Safety-related component

* By clicking on the article number, you will be taken to the product in the TIA Selection Tool cloud.

Signal boards

	Article number	
	Digital inputs Signal Board SB 1221, 4 DI 24VDC 200KHz Signal Board SB 1221, 4 DI 5VDC 200KHz SIPLUS S7-1200 SB 1221 4DI 24VDC SIPLUS S7-1200 SB 1221 4DI 5VDC	6ES7221-3BD30-0XB0 6ES7221-3AD30-0XB0 6AG1221-3BD30-5XB0 6AG1221-3AD30-5XB0
	Digital outputs Signal Board SB1222, 4 DQ 24VDC 200KHz Signal Board SB1222, 4 DQ 5VDC 200KHz SIPLUS S7-1200 SB 1222 4DQ 24VDC SIPLUS S7-1200 SB 1222 4DQ 5VDC	6ES7222-1BD30-0XB0 6ES7222-1AD30-0XB0 6AG1222-1BD30-5XB0 6AG1222-1AD30-5XB0
	Digital inputs/outputs Signal Board SB1223, 2 DI/2 DO Signal Board SB 1223, 2DI/2DQ 24V 200KHz Signal Board SB 1223, 2DI/2DQ 5V 200KHz SIPLUS S7-1200 SB 1223 2DI/2DQ, 24VDC SIPLUS S7-1200 SB 1223 2DI/2DQ, 24VDC SIPLUS S7-1200 SB 1223 2DI/2DQ, 24VDC SIPLUS S7-1200 SB 1223 2DI/2DQ 5VDC SIPLUS S7-1200 SB 1223 2DI/2DQ RAIL	6ES7223-0BD30-0XB0 6ES7223-3BD30-0XB0 6ES7223-3AD30-0XB0 6AG1223-0BD30-4XB0 6AG1223-0BD30-5XB0 6AG1223-3BD30-5XB0 6AG1223-3AD30-5XB0 6AG2223-0BD30-1XB0
	Analog inputs Signal Board SB 1231, 1 AI Signal Board SB 1231 RTD Signal Board SB 1231 TC, 1 AI SIPLUS S7-1200 SB 1231 1AI RTD	6ES7231-4HA30-0XB0 6ES7231-5PA30-0XB0 6ES7231-5QA30-0XB0 6AG1231-5PA30-5XB0
	Analog outputs Signal Board SB 1232, 1 AO SIPLUS S7-1200 SB 1232 1AQ SIPLUS S7-1200 SB 1232 1AQ	6ES7232-4HA30-0XB0 6AG1232-4HA30-5XB0 6AG1232-4HA30-4XB0

Communication boards

	Article number	
	Point-to-point Communication Board CB 1241, RS485 SIPLUS S7-1200 CB 1241 RS485 SIPLUS S7-1200 CB 1241 RS485 T1 RAIL	6ES7241-1CH30-1XB0 6AG1241-1CH30-5XB1 6AG2241-1CH30-1XB0

 : Safety-related component

* By clicking on the article number, you will be taken to the product in the TIA Selection Tool cloud.

Battery boards



	Article number
Battery Board BB 1297 f. CPU 12xx	6ES7297-0AX30-0XA0

Digital modules



	Article number
Digital input SM 1221	
Digital Input SM 1221, 8DI, 24V DC	6ES7221-1BF32-0XB0
Digital Input SM 1221, 16DI, 24V DC	6ES7221-1BH32-0XB0
SIPLUS S7-1200 SM 1221 16DI	6AG1221-1BH32-4XB0
SIPLUS S7-1200 SM 1221 16DI	6AG1221-1BH32-2XB0
SIPLUS S7-1200 SM 1221 8DI	6AG1221-1BF32-2XB0
SIPLUS S7-1200 SM 1221 8DI	6AG1221-1BF32-4XB0
SIPLUS S7-1200 SM 1221 8DI RAIL	6AG2221-1BF32-1XB0
Digital output SM 1222	
Digital Output SM 1222, 8 DO, Relay	6ES7222-1HF32-0XB0
Digital Output SM 1222, 8 DO, Changeover	6ES7222-1XF32-0XB0
Digital Output SM1222, 16 DO, Relay	6ES7222-1HH32-0XB0
Digital Output SM1222, 8 DO, 24V DC	6ES7222-1BF32-0XB0
Digital Output SM1222, 16 DO, 24V DC	6ES7222-1BH32-0XB0
Digital Output SM1222, 16DO, 24V DC sink	6ES7222-1BH32-1XB0
SIPLUS S7-1200 SM 1222 16DQ	6AG1222-1BH32-4XB0
SIPLUS S7-1200 SM 1222 16DQ	6AG1222-1BH32-2XB0
SIPLUS S7-1200 SM 1222 16DQ RLY	6AG1222-1HH32-4XB0
SIPLUS S7-1200 SM 1222 16DQ RLY	6AG1222-1HH32-2XB0
SIPLUS S7-1200 SM 1222 8DQ	6AG1222-1BF32-4XB0
SIPLUS S7-1200 SM 1222 8DQ	6AG1222-1BF32-2XB0
SIPLUS S7-1200 SM 1222 8DQ RAIL	6AG2222-1BF32-1XB0
SIPLUS S7-1200 SM 1222 8DQ RLY	6AG1222-1HF32-4XB0
SIPLUS S7-1200 SM 1222 8DQ RLY	6AG1222-1HF32-2XB0
SIPLUS S7-1200 SM 1222 8DQ RLY	6AG1222-1XF32-4XB0
SIPLUS S7-1200 SM 1222 8DQ RLY	6AG1222-1XF32-2XB0
SIPLUS S7-1200 SM 1222 8DQ RLY RAIL	6AG2222-1HF32-1XB0
Digital I/O SM 1223	
Digital I/O SM 1223, 8 DI / 8 DO	6ES7223-1BH32-0XB0
Digital I/O SM 1223, 16DI/16DO	6ES7223-1BL32-0XB0
Digital I/O SM 1223, 8DI/8DO	6ES7223-1PH32-0XB0
Digital I/O SM 1223, 16DI/16DO	6ES7223-1PL32-0XB0
Digital I/O SM 1223, 8DI AC/ 8DO Rly	6ES7223-1QH32-0XB0
Digital I/O SM 1223, 16DI/16DO sink	6ES7223-1BL32-1XB0
SIPLUS S7-1200 SM 1223 16DI/16DQ	6AG1223-1BL32-4XB0
SIPLUS S7-1200 SM 1223 16DI/16DQ	6AG1223-1BL32-2XB0
SIPLUS S7-1200 SM 1223 16DI/16DQ RAIL	6AG2223-1PL32-1XB0
SIPLUS S7-1200 SM 1223 16DI/16DQ RLY	6AG1223-1PL32-2XB0
SIPLUS S7-1200 SM 1223 16DI/16DQ RLY	6AG1223-1PL32-4XB0
SIPLUS S7-1200 SM 1223 8DI/8DQ	6AG1223-1BH32-2XB0
SIPLUS S7-1200 SM 1223 8DI/8DQ	6AG1223-1BH32-4XB0
SIPLUS S7-1200 SM 1223 8DI/8DQ RAIL	6AG2223-1BH32-1XB0

: Safety-related component

* By clicking on the article number, you will be taken to the product in the TIA Selection Tool cloud.

Digital modules

	Article number
SIPLUS S7-1200 SM 1223 8DI/8DQ RLY	6AG1223-1PH32-4XB0
SIPLUS S7-1200 SM 1223 8DI/8DQ RLY	6AG1223-1PH32-2XB0
SIPLUS S7-1200 SM 1223 8DI AC/8DQ RLY	6AG1223-1QH32-2XB0
SIPLUS S7-1200 SM 1223 8DI AC/8DQ RLY	6AG1223-1QH32-4XB0
Fail-safe digital modules SM 1226	
Digital Input SM 1226, F-DI 16x 24VDC	6ES7226-6BA32-0XB0
Digital Output SM 1226, F-DQ 4x 24VDC	6ES7226-6DA32-0XB0
Digital Output SM 1226, F-DQ 2x Relay	6ES7226-6RA32-0XB0
SIPLUS S7-1200 SM 1226 F-DQ 2xRelay	6AG1226-6RA32-5XB0
SIPLUS S7-1200 SM 1226 F-DQ 4x24VDC	6AG1226-6DA32-5XB0

Analog modules



SM 1231 analog input module

	Article number
Analog Input SM 1231, 4AI	6ES7231-4HD32-0XB0
Analog Input SM 1231, 8AI	6ES7231-4HF32-0XB0
Analog Input SM 1231, 4AI 16bit	6ES7231-5ND32-0XB0
S7-1200, analog Input SM 1231 RTD, 4 AI	6ES7231-5PD32-0XB0
S7-1200, analog Input SM 1231 RTD, 8 AI	6ES7231-5PF32-0XB0
S7-1200, analog Input SM 1231 TC, 4 AI	6ES7231-5QD32-0XB0
S7-1200, analog Input SM 1231 TC, 8 AI	6ES7231-5QF32-0XB0
SM 1238 Energy Meter 480V AC	6ES7238-5XA32-0XB0
SIPLUS S7-1200 SM 1231 4AI 13Bit	6AG1231-4HD32-4XB0
SIPLUS S7-1200 SM 1231 4AI 16Bit	6AG1231-5ND32-4XB0
SIPLUS S7-1200 SM 1231 4AI RTD 16Bit	6AG1231-5PD32-4XB0
SIPLUS S7-1200 SM 1231 4AI RTD 16Bit	6AG1231-5PD32-2XB0
SIPLUS S7-1200 SM 1231 4AI TC 16Bit	6AG1231-5QD32-4XB0
SIPLUS S7-1200 SM 1231 8AI 13Bit	6AG1231-4HF32-4XB0
SIPLUS S7-1200 SM 1231 8AI RTD 16Bit	6AG1231-5PF32-2XB0
SIPLUS S7-1200 SM 1231 8AI RTD 16Bit	6AG1231-5PF32-4XB0
SIPLUS S7-1200 SM 1231 8AI TC 16Bit	6AG1231-5QF32-4XB0
SIPLUS S7-1200 SM 1231 RTD RAIL	6AG2231-5PD32-1XB0

SM 1232 analog output module

Analog Output SM 1232, 4AO	6ES7232-4HD32-0XB0
Analog Output SM 1232, 2AO	6ES7232-4HB32-0XB0
SIPLUS S7-1200 SM 1232 2AQ 13Bit	6AG1232-4HB32-4XB0
SIPLUS S7-1200 SM 1232 4AQ 14Bit	6AG1232-4HD32-2XB0
SIPLUS S7-1200 SM 1232 4AQ 14Bit	6AG1232-4HD32-4XB0
SIPLUS S7-1200 SM 1232 4AQ RAIL	6AG2232-4HD32-1XB0

SM 1234 analog input/output module

Analog I/O SM 1234, 4AI/2AO	6ES7234-4HE32-0XB0
SIPLUS S7-1200 SM 1234 4AI/2AQ 13Bit	6AG1234-4HE32-2XB0
SIPLUS S7-1200 SM 1234 4AI/2AQ 13Bit	6AG1234-4HE32-4XB0
SIPLUS S7-1200 SM 1234 4AI/2AQ RAIL	6AG2234-4HE32-1XB1

: Safety-related component

* By clicking on the article number, you will be taken to the product in the TIA Selection Tool cloud.

Simulation modules



	Article number
S7-1200 Simulator Module SIM1274, 8 Inp	6ES7274-1XF30-0XA0
S7-1200 Simulator Module SIM1274, 14 Inp	6ES7274-1XH30-0XA0
S7-1200 Simulator S7-1217, 14 inputs	6ES7274-1XK30-0XA0
S7-1200 Potentiometer Module, 2 Pot Input	6ES7274-1XA30-0XA0

Communication modules



	Article number
S7-1200, SM1278, 4 X IO-Link Master	6ES7278-4BD32-0XB0
Communication Module cm 1241, RS232	6ES7241-1AH32-0XB0
Communication Module cm 1241, RS422/485	6ES7241-1CH32-0XB0
Communication module CM 1242-5	6GK7242-5DX30-0XE0
CM 1243-2 (AS-I V3.0)	3RK7243-2AA30-0XB0
Communication module CM 1243-5	6GK7243-5DX30-0XE0
Communication module RF120C	6GT2002-0LA00
Communication processor CP 1242-7	6GK7242-7KX31-0XE0
Communication processor CP 1243-1	6GK7243-1BX30-0XE0
Communication processor CP 1243-7 LTE EU	6GK7243-7KX30-0XE0
Communication processor CP 1243-7 LTE US	6GK7243-7SX30-0XE0
Communication processor CP 1243-8 IRC	6GK7243-8RX30-0XE0
DCM 1271 (AS-I DATA DECOUPL)	3RK7271-1AA30-0AA0
Compact Switch Module CSM 1277	6GK7277-1AA10-0AA0
SIPLUS	
SIPLUS NET CP 1242-7 V2	6AG1242-7KX31-7XE0
SIPLUS NET CSM 1277	6AG1277-1AA10-4AA0
SIPLUS NET CSM 1277	6AG1277-1AA10-2AA0
SIPLUS S7-1200 CM1241 RS232	6AG1241-1AH32-2XB0
SIPLUS S7-1200 CM 1241 RS232	6AG1241-1AH32-4XB0
SIPLUS S7-1200 CM1241 RS232 RAIL	6AG2241-1AH32-1XB0
SIPLUS S7-1200 CM 1241 RS422/485	6AG1241-1CH32-4XB0
SIPLUS S7-1200 CM 1241 RS422/485	6AG1241-1CH32-2XB0
SIPLUS S7-1200 CM1241 RS422/485 RAIL	6AG2241-1CH32-1XB0
SIPLUS S7-1200 CM 1242-5	6AG1242-5DX30-2XE0
SIPLUS S7-1200 CM 1242-5 RAIL	6AG2242-5DX30-1XE0
SIPLUS S7-1200 CM 1243-2	6AG1243-2AA30-7XB0
SIPLUS S7-1200 CM 1243-5	6AG1243-5DX30-2XE0
SIPLUS S7-1200 CM 1243-5 RAIL	6AG2243-5DX30-1XE0
SIPLUS S7-1200 CP 1243-1	6AG1243-1BX30-2AX0
SIPLUS S7-1200 CP 1243-1 RAIL	6AG2243-1BX30-1XE0
SIPLUS S7-1200 SM 1278 IO-Link Master	6AG1278-4BD32-2XB0
SIPLUS S7-1200 SM 1278 IO-Link Master	6AG1278-4BD32-4XB0

: Safety-related component

* By clicking on the article number, you will be taken to the product in the TIA Selection Tool cloud.

Technology modules



	Article number
SIWAREX WP231 WEIGHING ELECTRONIC	7MH4960-2AA01
SIWAREX WP241 WEIGHING ELECTRONIC	7MH4960-4AA01
SIWAREX WP251 WEIGHING ELECTRONIC	7MH4960-6AA01
SM1281_Condition_Monitoring	6AT8007-1AA10-0AA0

Power supplies



	Article number
SIMATIC PM1207/1AC/24VDC/2.5A SIPLUS	6EP1332-1SH71
SIPLUS POWER MODUL PM1207	6AG1332-1SH71-4AA0
SIPLUS POWER MODUL PM1207	6AG1332-1SH71-7AA0

Accessories



	Article number
Memory card	
SIMATIC S7 memory card, 4 MB	6ES7954-8LC03-0AA0
SIMATIC S7 Memory Card, 12 MB	6ES7954-8LE03-0AA0
SIMATIC S7 Memory Card, 24 MB	6ES7954-8LF03-0AA0
SIMATIC S7 Memory Card, 256 MB	6ES7954-8LL03-0AA0
SIMATIC S7 Memory Card, 2 GB	6ES7954-8LP03-0AA0
SIMATIC S7 Memory Card, 32 GB	6ES7954-8LT03-0AA0
Manuals	

	Article number
Terminal block	
Connector Block, 7 Poles, Tin (4/PK)	6ES7292-2AG30-0XA0
Connector keyed, 7 Poles, Tin (4/PK)	6ES7292-2AG40-0XA0
Connector keyed, 7 Poles, Tin (4/PK)	6ES7292-2AG40-0XA1
Connector keyed, 7 Poles, Tin (4/PK)	6ES7292-2AG40-0XA2
Connector Block, 8 Terminal, Tin (4/PK)	6ES7292-2AH30-0XA0
Connector Block, 8 Poles, Tin (4/PK)	6ES7292-2AH40-0XA0
Connector Block, 10 Poles, Tin (4/PK)	6ES7292-2AK30-0XA0
Connector Block, 11 Poles, Tin (4/PK)	6ES7292-2AL30-0XA0
Connector Block, 11 Poles, Tin (4/PK)	6ES7292-2AL40-0XA0
Connector Block, 12-pole, tin (4/PK)	6ES7292-2AM30-0XA0
Connector Block, 12-pole, tin (4/PK)	6ES7292-2AM40-0XA0
Connector Block, 14 Poles, Tin (4/PK)	6ES7292-2AP30-0XA0
Connector Block, 14 Poles, Tin (4/PK)	6ES7292-2AP40-0XA0
Connector Block, 16 Poles, Tin (4/PK)	6ES7292-2AR30-0XA0
Connector Block, 18 Poles, Tin (4/PK)	6ES7292-2AT30-0XA0
Connector Block, 20-pole, tin (4/PK)	6ES7292-2AV30-0XA0
Connector Block, 20-pole, tin (4/PK)	6ES7292-2AV40-0XA0
Connector Block, 3-pole, gold (4/PK)	6ES7292-2BC30-0XA0

: Safety-related component

* By clicking on the article number, you will be taken to the product in the TIA Selection Tool cloud.

Accessories

	Article number
Terminal block, 6 Poles, gold (4/PK)	6ES7292-2BF30-0XB0
Connector Block, 7 Poles, Gold (4/PK)	6ES7292-2BG30-0XA0
Connector Block, 11 Poles, Gold (4/PK)	6ES7292-2BL30-0XA0
Connector Block, 7 Terminal, Tin (4/PK)	6ES7292-1AG30-0XA0
Connector keyed, 7 Terminal, Tin (4/PK)	6ES7292-1AG40-0XA0
Connector keyed, 7 Terminal, Tin (4/PK)	6ES7292-1AG40-0XA1
Connector keyed, 7 pins, Tin (4/Pk)	6ES7292-1AG40-0XA2
Connector Block, 8 Terminal, Tin (4/PK)	6ES7292-1AH30-0XA0
Connector Block, 8 Terminal, Tin (4/PK)	6ES7292-1AH40-0XA0
Connector Block, 10 Terminal, Tin (4/PK)	6ES7292-1AK30-0XA0
Connector Block, 11 Terminal, Tin (4/PK)	6ES7292-1AL30-0XA0
Connector Block, 11 Terminal, Tin (4/PK)	6ES7292-1AL40-0XA0
Connector Block, 12 Terminal, Tin (4/PK)	6ES7292-1AM30-0XA0
Connector Block, 12 Terminal, Tin (4/PK)	6ES7292-1AM40-0XA0
Connector Block, 14 Terminal, Tin (4/PK)	6ES7292-1AP30-0XA0
Connector Block, 14 Terminal, Tin (4/PK)	6ES7292-1AP40-0XA0
Connector Block, 16 Terminal, Tin (4/PK)	6ES7292-1AR30-0XA0
Connector Block, 18 Terminal, Tin (4/PK)	6ES7292-1AT30-0XA0
Connector Block, 20 Terminal, Tin (4/PK)	6ES7292-1AV30-0XA0
Connector Block, 20 Terminal, Tin (4/PK)	6ES7292-1AV40-0XA0
Connector Block, 3 Terminal, Gold (4/PK)	6ES7292-1BC30-0XA0
Terminal block, 6 Terminal, gold (4/PK)	6ES7292-1BF30-0XA0
Terminal block, 6 Terminal, gold (4/PK)	6ES7292-1BF30-0XB0
Connector Block, 7 Terminal, Gold (4/PK)	6ES7292-1BG30-0XA0
Connector Block, 11 Terminal, Gold(4/PK)	6ES7292-1BL30-0XA0
TeleService	
TS ADAPTER IE BASIC SIMATIC TELESERVICE	6ES7972-0EB00-0XA0
TS ADAPTER IE ADV. SIMATIC TELESERVICE	6ES7972-0EA00-0XA0
TeleService module modem	6ES7972-0MM00-0XA0
TeleService module ISDN	6ES7972-0MD00-0XA0
TeleService module RS232	6ES7972-0MS00-0XA0
Antenna ANT794-4MR, 2G/3G/4G EU networks	6NH9860-1AA00
Antenna ANT 794-3M, 2G networks	6NH9870-1AA00
Strain relief	
S7-1200 Single Port RJ45 Strain Relief	6ES7290-3AA30-0XA0
S7-1200 Dual Port RJ45 Strain Relief	6ES7290-3AB30-0XA0
SIMATIC S7-1200, Expansion Cable 2.0M	6ES7290-6AA30-0XA0
Repeater RS485 f. PROFIBUS/MPI	6ES7972-0AA02-0XA0
Diagnostic repeater f. PROFIBUS-DP,	6ES7972-0AB01-0XA0
SIPLUS	
SIPLUS Diagnose-Repeater fuer Profibus	6AG1972-0AB01-4XA0
SIPLUS DP RS485-Repeater	6AG1972-0AA02-7XA0
Accessories M8, M12	
AS-INTERFACE ACCESSORIES	3RK1901-1KA00
M12 PROFIBUS SOCKET ANGLED	3RK1902-4HB15-5AA0
M12 PROFIBUS SOCKET ANGLED	3RK1902-4HB50-5AA0
M12 PROFIBUS SOCKET ANGLED	3RK1902-4HC01-5AA0
M12 - M12 CABLE 1.5M 3 POLE	3RK1902-4PB15-3AA0
ET200, Y cable	6ES7194-6KA00-0XA0
Conn. Cable IO-Link, 2 X M12-4pin, 5m	6GT2891-4MH50
Conn. Cable IO-Link, 2 X M12-4pin, 10m	6GT2891-4MN10
Control Cable 5 core cable sold by meter	6XV1801-2C
Control Connecting Cable M12/M12, 0,5m	6XV1801-2CE50
Control Connecting Cable M12/M12, 1,0m	6XV1801-2CH10
Control Connecting Cable M12/M12, 1,0m	6XV1801-2CH15


 : Safety-related component

* By clicking on the article number, you will be taken to the product in the TIA Selection Tool cloud.

Accessories

	Article number
Control Connecting Cable M12/M12, 2,0m	6XV1801-2CH20
Control Connecting Cable M12/M12, 3,0m	6XV1801-2CH30
Control Connecting Cable M12/M12, 5,0m	6XV1801-2CH50
Control Connecting Cable M12/M12, 10,0m	6XV1801-2CN10
Control Connecting Cable M12/M12, 15,0m	6XV1801-2CN15
Sensors	
SIPLUS CMS2000 VIB-SENSOR S01	6AT8002-4AB00
SIPLUS CMS VIB-SENSOR S02	6AT8008-2AA00-0AA0
SIPLUS CMS VIB-SENSOR S03	6AT8008-2AA02-0AA0
Cable	
SIPLUS CMS2000 CABLE 3m	6AT8002-4AC03
SIPLUS CMS2000 CABLE 10m	6AT8002-4AC10
SIPLUS CMS CABLE 30m	6AT8008-2BA12-0AA0

Engineering software and software options

	Article number	
	SIMATIC STEP 7 Basic V17 (Download)	6ES7822-0AE07-0YA5
	SIMATIC STEP 7 Basic V17 (Package)	6ES7822-0AA07-0YA5
	SIMATIC STEP 7 Safety Basic V17 (Download)	6ES7833-1FB17-0YH5
	SIMATIC STEP 7 Safety Basic V17 (Package)	6ES7833-1FB17-0YA5
	STEP 7 Basic SW Update Service, 1 Year	6ES7822-0AA00-0YL0
	STEP 7 Basic TIA Portal SUS DL	6ES7822-0AE00-0YY0
	STEP7 Safety Basic, SUS Download	6ES7833-1FD00-0YN2
	STEP7 Safety Basic, SW Update Service	6ES7833-1FD00-0YX2

 : Safety-related component

* By clicking on the article number, you will be taken to the product in the TIA Selection Tool cloud.

Published by
Siemens AG

Digital Industries
Factory Automation
P.O. box 4848
90026 Nuremberg
Germany

For U.S. only:
Siemens Industry Inc.

100 Technology Drive
Alpharetta, GA 30005
United States

Copyright© 2022 Siemens

The TIA SELECTION TOOL and all its editions are made available to you at no charge. We therefore do not assume any warranty, in particular for the accuracy, correctness, completeness, availability or usability of this tool. Our liability for damages resulting from using the examples, help notes, programs, configuration and performance data, etc. described in this TIA SELECTION TOOL and all its editions regardless of the legal background is excluded unless required by law, e.g. in cases of willful misconduct, gross negligence, personal injury or death, failure to achieve guaranteed characteristics or fraudulent concealment of a defect or in case of breach of fundamental contractual obligations. Distribution or reproduction of this TIA SELECTION TOOL and all its editions or excerpts from it is prohibited unless expressly permitted by Siemens. The latest firmware and hardware versions are configured in the TIA Selection Tool.